





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AD1	REVISED PER ECN-22-174625	16SEP2022	RK	MF



RECOMMENDED HOLE LAYOUT

1. .000100 BRIGHT TIN-LEAD OVER .000050 NICKEL.
2. POINT OF MEASUREMENT FOR PLATING THICKNESS.
3. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
4. ON ASSEMBLIES WITH FOUR OR MORE POSITIONS,
TWO POLARIZATION SLOTS.
ON ASSEMBLIES WITH TWO OR THREE POSITIONS,
ONE POLARIZATION SLOT.
5. SELECT POST TAILS FORMED TO PROVIDE CONNECTOR HOLD DOWN
UNTIL SOLDERED. CONFIGURATION ACCEPTS 0.69[.027]-2.03[.080]
THICK PRINTED CIRCUIT BOARD. (SEE DETAIL Z).
6. .000100 BRIGHT TIN OVER .000050 NICKEL.
7. PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
8. .000100 MATTE TIN OVER .000050 NICKEL.
9. HIGH TEMPERATURE CONFIGURATION.
10. STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY
11. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINIS
12. 0.25 [.010] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF

11		9	6	23.37 [.920]	25.27 [.995]	8	9	3-103669-0
		9	6	8.13 [.320]	10.03 [.395]	2	3	2-103669-9
		9	6	15.75 [.620]	17.65 [.695]	5	6	2-103669-8
		9	6	13.21 [.520]	15.11 [.595]	4	5	2-103669-7
		9	6	10.67 [.420]	12.57 [.495]	3	4	2-103669-6
		9	6	5.59 [.220]	7.49 [.295]	1	2	2-103669-5
11	OBSOLETE	9	1	64.01 [2.520]	65.91 [2.595]	24	25	2-103669-4
11	OBSOLETE	9	1	61.47 [2.420]	63.37 [2.495]	23	24	2-103669-3
11	OBSOLETE	9	1	58.93 [2.320]	60.83 [2.395]	22	23	2-103669-2
11	OBSOLETE	9	1	56.39 [2.220]	58.29 [2.295]	21	22	2-103669-1
11	OBSOLETE	9	1	53.85 [2.120]	55.75 [2.195]	20	21	2-103669-0
11		9	1	51.31 [2.020]	53.21 [2.095]	19	20	1-103669-9
	OBSOLETE	9	1	48.77 [1.920]	50.67 [1.995]	18	19	1-103669-8
	OBSOLETE	9	1	46.23 [1.820]	48.13 [1.895]	17	18	1-103669-7
11		9	1	43.69 [1.720]	45.59 [1.795]	16	17	1-103669-6
		9	1	41.15 [1.620]	43.05 [1.695]	15	16	1-103669-5
11	OBSOLETE	9	1	38.61 [1.520]	40.51 [1.595]	14	15	1-103669-4
		9	1	36.07 [1.420]	37.97 [1.495]	13	14	1-103669-3
		9	1	33.53 [1.320]	35.43 [1.395]	12	13	1-103669-2
		9	1	30.99 [1.220]	32.89 [1.295]	11	12	1-103669-1
		9	1	28.45 [1.120]	30.35 [1.195]	10	11	1-103669-0
		9	1	25.91 [1.020]	27.81 [1.095]	9	10	103669-9
		9	1	23.37 [.920]	25.27 [.995]	8	9	103669-8
		9	1	20.83 [.820]	22.73 [.895]	7	8	103669-7
		9	1	18.29 [.720]	20.19 [.795]	6	7	103669-6
		9	1	15.75 [.620]	17.65 [.695]	5	6	103669-5
		9	1	13.21 [.520]	15.11 [.595]	4	5	103669-4
		9	1	10.67 [.420]	12.57 [.495]	3	4	103669-3
		9	1	8.13 [.320]	10.03 [.395]	2	3	103669-2
		9	1	5.59 [.220]	7.49 [.295]	1	2	103669-1
		REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 3-5-91 S. SHUEY CHK 2-14-92 M. RIDER		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 R/LC ± 1 R/LC ± 1.08 ± 0.1(0.05) 4 R/LC ± 4 R/LC ± ANGLES ± ±		NAME HDR ASSY, VERT, SR 2.54 [100] C/L 0.64 [025] SQ POST WITH PLZEN, AMPMODU MTE	
MATERIAL HOUSING: LCP, CONTACTS: BRASS		FINISH SEE TABLE		PRODUCT SPEC 108-25034 APPLICATION SPEC 114-25026	
		WEIGHT —		SIZE: CAGE CODE: DRAWING NO A1 00779 C= 10366N	
		CUSTOMER DRAWING		SCALE: 4:1 SHEET 1 of 2 REV AD	

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

OBSOLETE

11

9 10	8	64.01 [2.520]	65.91 [2.595]	24	25	7-103669-4
9 10	8	61.47 [2.420]	63.37 [2.495]	23	24	7-103669-3
9 10	8	58.93 [2.320]	60.83 [2.395]	22	23	7-103669-2
9 10	8	56.39 [2.220]	58.29 [2.295]	21	22	7-103669-1
9 10	8	53.85 [2.120]	55.75 [2.195]	20	21	7-103669-0
9 10	8	51.31 [2.020]	53.21 [2.095]	19	20	6-103669-9
9 10	8	48.77 [1.920]	50.67 [1.995]	18	19	6-103669-8
9 10	8	46.23 [1.820]	48.13 [1.895]	17	18	6-103669-7
9 10	8	43.69 [1.720]	45.59 [1.795]	16	17	6-103669-6
9 10	8	41.15 [1.620]	43.05 [1.695]	15	16	6-103669-5
9 10	8	38.61 [1.520]	40.51 [1.595]	14	15	6-103669-4
9 10	8	36.07 [1.420]	37.97 [1.495]	13	14	6-103669-3
9 10	8	33.53 [1.320]	35.43 [1.395]	12	13	6-103669-2
9 10	8	30.99 [1.220]	32.89 [1.295]	11	12	6-103669-1
9 10	8	28.45 [1.120]	30.35 [1.195]	10	11	6-103669-0
9 10	8	25.91 [1.020]	27.81 [1.095]	9	10	5-103669-9
9 10	8	23.37 [.920]	25.27 [.995]	8	9	5-103669-8
9 10	8	20.83 [.820]	22.73 [.895]	7	8	5-103669-7
9 10	8	18.29 [.720]	20.19 [.795]	6	7	5-103669-6
9 10	8	15.75 [.620]	17.65 [.695]	5	6	5-103669-5
9 10	8	13.21 [.520]	15.11 [.595]	4	5	5-103669-4
9 10	8	10.67 [.420]	12.57 [.495]	3	4	5-103669-3
9 10	8	8.13 [.320]	10.03 [.395]	2	3	5-103669-2
9 10	8	5.59 [.220]	7.49 [.295]	1	2	5-103669-1
REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.

11

OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
HOUSING: LCP,
CONTACTS: BRASS

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0. PLC
1. PLC
2. PLC
3. PLC
4. PLC
ANGLES

± -
± -
± -
± -
± -

0.13[.005]

SEE TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S. SHUEY
CHK
M. RIDER
APVD
M. RIDER

3-5-91
2-14-92
2-14-92

PRODUCT SPEC
108-25034
APPLICATION SPEC
114-25026

WEIGHT
—

CUSTOMER DRAWING

SCALE
4:1

SHEET
2

OF
2

REV
AD1

TE Connectivity

HDR ASSY, VERT, SR
2.54 .100 C/L 0.64 .025 SQ POST
WITH PLZN, AMPMODU MTE

SIZE
A1

CAGE CODE
00779

DRAWING NO
103669

RESTRICTED TO
—

4805 (1/15)