




LOC	DIST	REVISIONS				
AD	00	P	LTR	DESCRIPTION	DATE	DWN APVD
			W	ECO-06-029064	14DEC06	MB JG
			W1	REVISED PER ECO-09-020689	25AUG09	KK AEG

8	2-104257-4	25	7-103734-4
	2-104257-3	24	7-103734-3
	2-104257-2	23	7-103734-2
	2-104257-1	22	7-103734-1
	2-104257-0	21	7-103734-0
	1-104257-9	20	6-103734-9
	1-104257-8	19	6-103734-8
	1-104257-7	18	6-103734-7
	1-104257-6	17	6-103734-6
	1-104257-5	16	6-103734-5
	1-104257-4	15	6-103734-4
	1-104257-3	14	6-103734-3
	1-104257-2	13	6-103734-2
7	2-104257-4	25	2-103734-4
	2-104257-3	24	2-103734-3
	2-104257-2	23	2-103734-2
	2-104257-1	22	2-103734-1
	2-104257-0	21	2-103734-0
	1-104257-9	20	1-103734-9
	1-104257-8	19	1-103734-8
	1-104257-7	18	1-103734-7
	1-104257-6	17	1-103734-6
	1-104257-5	16	1-103734-5
	1-104257-4	15	1-103734-4
	1-104257-3	14	1-103734-3
	1-104257-2	13	1-103734-2
	1-104257-1	12	1-103734-1
	1-104257-0	11	1-103734-0
	104257-9	10	103734-9
	104257-8	9	103734-8
	104257-7	8	103734-7
	104257-6	7	103734-6
	104257-5	6	103734-5
	104257-4	5	103734-4
	104257-3	4	103734-3
	104257-2	3	103734-2
	104257-1	2	103734-1

SUPERSEDED BY 1-103958-1
SUPERSEDED BY 1-103958-0
SUPERSEDED BY 103958-9
SUPERSEDED BY 103958-8
SUPERSEDED BY 103958-7
SUPERSEDED BY 103958-6
SUPERSEDED BY 103958-5
SUPERSEDED BY 103958-4
SUPERSEDED BY 103958-3
SUPERSEDED BY 103958-2
SUPERSEDED BY 103958-1

- 1
- CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS
- 2
- USE WITH #22-#26 AWG WIRE SIZE, .054/.030 INSULATION DIAMETER, .015 MAXIMUM INSULATION THICKNESS
- 3
- THE DIMENSION APPLIES WITH THE FORWARD PRELOAD STOP IN CONTACT WITH THE HOUSING SURFACE
- 4
- POINT OF MEASUREMENT FOR PLATING THICKNESS
- 5
- FOR STRIP ASSEMBLIES SEE PART NUMBER 103958
- 6
- POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS)
- 7
- FINISH: CONTACTS- .000030 GOLD IN THE CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD ON THE TERMINATION AREA, ALL OVER .000050 NICKEL
- 8
- FINISH: CONTACTS- .000030 GOLD IN THE CONTACT AREA, .000050-.000100 MATTE TIN ON THE TERMINATION AREA, ALL OVER .000050 NICKEL
- 9
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL : HOUSING- FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK

CONTACTS-PHOS. BRONZE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	.02
3 PLC	±	.005
4 PLC	±	-
ANGLES	±	-

FINISH

SEE TABLE

DWN L MAYER 04 NOV 1986

CHK P. DE JONG 11-12-86

APVD P. DE JONG 11-12-86

PRODUCT SPEC 108-25034

APPLICATION SPEC 114-25026

WEIGHT -

CUSTOMER DRAWING

Tyco Electronics Corporation Harrisburg, Pa 17105-3608

NAME RCPT ASSY, AMPMODU MTE, SINGLE, LATCHED & POLARIZED, FOR #22-#26 AWG WIRE SIZE

SIZE A2 CAGE CODE 00779 DRAWING NO 103734

RESTRICTED TO -

SCALE 4:1 SHEET 1 OF 1 REV W1