

D25, DH25 and DHR25 Series, Rated up to 100 Amps, 115/200 VAC, 400 Hz

Product Facts

- 3PDT NO
- Gasket sealed or Hermetically sealed
- Auxiliary contacts available
- Meets many requirements of MIL-PRF-6106



Performance Data

Electrical Characteristics Contact Arrangement — 3PDT NO Rated Operating Voltage — 115/200 VAC, 400 Hz, 3 phase Resistive Rating — 100 Amps Inductive Rating — 100 Amps

General Characteristics Temperature Range — -55°C to +85°C

Operating Cycles (Life) at Rated Resistive Load, Min. -50,000 cycles

Operating Cycles (Life) Mechanical, Min. — 100,000 cycles Dielectric Strength — All Circuits to Ground — 1,500 Vrms Circuit to Circuit — 1,500 Vrms

Coil to Ground and Aux. Contacts -1,000 Vrms

Insulation Resistance, Initial -100 megohm min.

Altitude -D-25 — 50,000 ft. DH-25, DHR-25 - 80,000 ft.

Weight, Max. - 2.20 to 2.75 lbs Sinusoidal Vibration 10 G @ 70 to 2,000 Hz **Shock, Max.** — 25 G Operate Time @ Nom. Voltage, Max. — 35 msec Release Time @ Nom. Voltage, Max. — 35 msec Bounce Time @ Nom. Voltage, Max. — 5 msec

Coil Characteristics

Duty Cycle -VAC 400 Hz — AC (Type A, See diagram below) Vdc - Continuous (Type B, See diagram below) Vdc — Continuous with suppression (Type C, See diagram below)


Operating Voltage, Nom. — VAC 400 Hz - 115 VAC Vdc - 28 Vdc

Pickup Voltage @ 25°C, Max. — VAC 400 Hz - 103.5 VAC Vdc — 18 Vdc

Dropout Voltage @ 25°C, Max. — VAC 400 Hz — 5 to 45 VAC Vdc — 1.5 to 7 Vdc

Coil Resistance ±20% @ 25°C ----VAC 400 Hz - N/A Vdc — 175 Ohms

Coil Type



A – AC

For factory-direct application assistance, phone 419-521-9500 or fax 419-526-2749.

Catalog 5-1773450-5 Revised 3-13

Dimensions are shown for reference purposes only. Specifications subject to change.

Dimensions are in millimeters unless otherwise specified.

+X1 O

-X2 O

B — Continuous

OBSERVE

POLARITY

USA: +1 800 522 6752 Asia Pacific: +86 0 400 820 6015 UK: +44 800 267 666 For additional support numbers please visit www.te.com

+X1 O

-X2 (

C — Continuous with Suppression


OBSERVE

POLARITY


6 - 27




D25, DH25 and DHR25 Series, Rated up to 100 Amps, 115/200 VAC, 400 Hz (Continued)




Mounting Style A



Mounting Style B





For factory-direct application assistance, phone 419-521-9500 or fax 419-526-2749.

Mounting Style C

6-28

Catalog 5-1773450-5 Revised 3-13

reference purposes only. Specifications subject to change.

Dimensions are shown for

Dimensions are in millimeters unless otherwise specified.


USA: +1 800 522 6752 Asia Pacific: +86 0 400 820 6015 UK: +44 800 267 666


For additional support numbers please visit www.te.com





D25, DH25 and DHR25 Series, Rated up to 100 Amps, 115/200 VAC, 400 Hz (Continued)

Circuit Configurations (Consult factory for other available circuit configurations)









Circuit Configuration 1

Circuit Configuration 2

Circuit Configuration 3

Circuit Configuration 4

HARTMAN Part Number	Construction Type	Mounting Style	Coil Type	Circuit Config.	TE Part Number
D-25BD	Gasket/Vented	A	В	1	1616034-3
DH-25B	Hermetically Sealed	С	В	4	1616037-2
DH-25BA	Hermetically Sealed	В	В	2	1616037-3
DHR-25BG	Hermetically Sealed	А	A	3	1-1616037-5

For factory-direct application assistance, phone 419-521-9500 or fax 419-526-2749.

Catalog 5-1773450-5 Revised 3-13 Dimensions are shown for reference purposes only. Specifications subject to change. Dimensions are in millimeters unless otherwise specified.

USA: +1 800 522 6752 Asia Pacific: +86 0 400 820 6015 UK: +44 800 267 666 For additional support numbers please visit www.te.com

S

6-29