







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	AF	REVISED PER ECO-20-001327	04JUN2020	SB	JO

D




- 1 0.00254-0.00508 [$.000100-.000200$] BRIGHT TIN-LEAD OVER 0.00127 [$.000050$] NICKEL.
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3 THESE DIMENSIONS APPLY WHERE THE POST INTERSECTS THE HOUSING.
- 4 ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS.
- 5 SELECT POST TAILS FORMED TO PROVIDE CONNECTOR HOLD DOWN UNTIL SOLDERED.CONFIGURATION ACCEPTS 0.69-2.03 [$.027-.080$] THICK PRINTED CIRCUIT BOARD. (SEE DETAIL Z).
- 6 MATERIAL: HOUSING- LCP, COLOR-BLACK. POSTS- BRASS.
- 7 0.00254-0.00508 [$.000100-.000200$] BRIGHT TIN OVER 0.00127 [$.000050$] NICKEL.
- 8 HIGH TEMPERATURE CONFIGURATION.
- 9 0.00254-0.00508 [$.000100-.000200$] MATTE TIN OVER 0.00127 [$.000050$] NICKEL.
- 10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.
- 11 0.25 [$.010$] RECESS PERMISSIBLE IN THIS AREA FOR MOLD SHUT OFF

C



SECTION A-A

10	OBSOLETE	8	9	27.81 [1.095]	25.91 [1.020]	22.86 [.900]	9	10	5-104450-9		
		8	9	25.27 [.995]	23.37 [.920]	20.32 [.800]	8	9	5-104450-8		
10	OBSOLETE	8	9	22.73 [.895]	20.83 [.820]	17.78 [.700]	7	8	5-104450-7		
		8	9	20.19 [.795]	18.29 [.720]	15.24 [.600]	6	7	5-104450-6		
		8	9	17.65 [.695]	15.75 [.620]	12.7 [.500]	5	6	5-104450-5		
		8	9	15.11 [.595]	13.21 [.520]	10.16 [.400]	4	5	5-104450-4		
		8	9	12.57 [.495]	10.67 [.420]	7.62 [.300]	3	4	5-104450-3		
		8	9	10.03 [.395]	8.13 [.320]	5.08 [.200]	2	3	5-104450-2		
		8	9	7.49 [.295]	5.59 [.220]	2.54 [.100]	1	2	5-104450-1		
		7	7	20.19 [.795]	18.29 [.720]	15.24 [.600]	6	7	1-104450-3		
10	OBSOLETE	7	7	15.11 [.595]	13.21 [.520]	10.16 [.400]	4	5	1-104450-2		
		7	7	10.03 [.395]	8.13 [.320]	5.08 [.200]	2	3	1-104450-1		
		7	7	12.57 [.495]	10.67 [.420]	7.62 [.300]	3	4	1-104450-0		
		1	1	27.81 [1.095]	25.91 [1.020]	22.86 [.900]	9	10	104450-9		
10	OBSOLETE	1	1	25.27 [.995]	23.37 [.920]	20.32 [.800]	8	9	104450-8		
		1	1	22.73 [.895]	20.83 [.820]	17.78 [.700]	7	8	104450-7		
		1	1	20.19 [.795]	18.29 [.720]	15.24 [.600]	6	7	104450-6		
		1	1	17.65 [.695]	15.75 [.620]	12.7 [.500]	5	6	104450-5		
		1	1	15.11 [.595]	13.21 [.520]	10.16 [.400]	4	5	104450-4		
		1	1	12.57 [.495]	10.67 [.420]	7.62 [.300]	3	4	104450-3		
		1	1	10.03 [.395]	8.13 [.320]	5.08 [.200]	2	3	104450-2		
		1	1	7.49 [.295]	5.59 [.220]	2.54 [.100]	1	2	104450-1		
		REMARKS		PLATING		D	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER



RECOMMENDED HOLE LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R BROWN	09FEB01	 TE Connectivity			
DIMENSIONS: mm			CHK K WRIGHT	09FEB01				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD K WRIGHT	09FEB01	NAME HEADER ASSY, AMPMODU MTE, VERTICAL, WITH LATCH, SINGLE ROW, .100 CL, .025 SO POSTS, PCB ORIENTATION, AND RETENTIVE POSTS		
				PRODUCT SPEC				
				108-25034				
				APPLICATION SPEC				
MATERIAL: SEE NOTE 6	FINISH: SEE TABLE			WEIGHT 0.000000	SIZE A1	CAGE CODE 00779	DRAWING NO 104450	RESTRICTED TO —
CUSTOMER DRAWING					SCALE 4:1	SHEET 1 OF 1	REV AF	