

Versatile Protective Coverings for Automotive Components












NETM Tubing Specially designed for use in electrical harnesses.



NETM Tubing

Non heat-shrink tubing designed for electrical harnessing needs. Particularly suitable for the agressive environment of car engines, NETM can withstand higher temperatures than traditional PVC materials whilst retaining its high level of performance.

NETM1000 is the more flexible product, enabling it to be easily routed through engine spaces. NETM2000 offers greater mechanical strength and excellent abrasion resistance.

NETM products are durable non-shrinking polyolefin tubings which remain heat resistant up to at least 130°C. Specifically designed for use in electrical harnesses, NETM tubings are flame retarded and offer excellent abrasion resistance.

NETM1000 is a more flexible 125 °C product allowing it to follow wiring bundles routed in tight bends around underbonnet components. NETM2000 is designed for higher temperature applications rated up to 150 °C.

Benefits

- Excellent heat resistance
- Flexible
- Good mechanical strength
- RoHS/ELV compliant


Protection ProductsMechanical Protection

Non Heat-Shrink Harness Tubing

Product Features

NETM Tubing

■ Operating temperature from -55°C up to +135°C (NETM-1000) from -40°C up to +150°C (NETM-2000)



Product Dimensions and Ordering Information

	Inside Diameter D (nom) Supplied mm	Wall Thickness W (nom) mm	Product Description
NETM1000	3	0.5	NETM1000-3-0-SP
	4	0.5	NETM1000-4-0-SP
	5	0.5	NETM1000-5-0-SP
	6	0.5	NETM1000-6-0-SP
	8	0.5	NETM1000-8-0-SP
	10	0.5	NETM1000-10-0-SP
	12	0.5	NETM1000-12-0-SP
	14	0.5	NETM1000-14-0-SP
NETM2000	6	0.5	NETM2000-6-0-SP
	8	0.5	NETM2000-8-0-SP
	10	0.5	NETM2000-10-0-SP
	12	0.5	NETM2000-12-0-SP
Standard Colour	Black (0)		



Operating Temperature Range



Operating Temperature Range