

TFE and TFER

High-Temperature, Chemically Inert, Modified Tubing made of PTFE

Product Facts

- Shrink ratio: 1.8:1 (TFE) 3.2:1 (TFER)
- High flame-resistance
- Excellent chemical resistance
- RoHS compliant



Applications

Designed to provide insulation and mechanical protection in severe chemical and thermal environments. Used to cover hydraulic hose and couplings to prevent contamination and corrosion. The high mechanical strength and extremely low coefficient of friction make it good for reducing damage to bearing shafts and similar applications.

Installation

Minimum shrink temperature: 330°C [625°F] Minimum full recovery temperature: 340°C [644°F]

Operating Temperature Range

-67°C to 250°C [-88.6°F to 482°F]

Specifications/Approvals

Series	Military	Raychem
TFE, TFER	AMS-DTL-23053/12*, Classes 3 and 5 Def. Stan. 59-97 Type 5A (TFE) Def. Stan. 59-97 Type 5B (TFER)	RW-2055 (TFE) RW-2054 (TFER)

^{*}Formerly MIL-I-23053/12 and MIL-DTL-23053/12.

Available in:	Americas	Europe	Asia Pacific	
			•	



TFE and TFER (Continued)

Product Dimensions TFE

	Inside Diameter		Wall Thickness**	
Size	Minimum Expanded as Supplied	Maximum Recovered After Heating	Nominal Recovered After Heating	
30	0.8 [0.032]	0.38 [0.015]	0.23 [0.009]	
28	0.9 [0.035]	0.46 [0.018]	0.23 [0.009]	
26	1.1 [0.043]	0.56 [0.022]	0.25 [0.010]	
24	1.2 [0.047]	0.68 [0.027]	0.25 [0.010]	
22	1.4 [0.055]	0.81 [0.032]	0.30 [0.012]	
20	1.5 [0.059]	0.99 [0.039]	0.30 [0.012]	
18	1.9 [0.075]	1.24 [0.049]	0.30 [0.012]	
16	2.3 [0.091]	1.55 [0.061]	0.30 [0.012]	
14	3.0 [0.118]	1.83 [0.072]	0.30 [0.012]	
12	3.8 [0.150]	2.26 [0.089]	0.30 [0.012]	
10	4.8 [0.189]	2.84 [0.112]	0.30 [0.012]	
8	6.1 [0.240]	3.58 [0.141]	0.38 [0.015]	
6	7.6 [0.299]	4.52 [0.178]	0.38 [0.015]	
4	9.4 [0.370]	5.69 [0.224]	0.38 [0.015]	
2	10.9 [0.429]	7.06 [0.278]	0.38 [0.015]	
0	11.9 [0.469]	8.81 [0.347]	0.38 [0.015]	

^{**}Wall thickness will be less if tubing recovery is restricted during shrinkage.

TFER

Size	Inside Diameter		Wall Thickness**	
	Minimum Expanded as Supplied	Maximum Recovered After Heating	Nominal Recovered After Heating	
5/64	2.0 [0.079]	0.6 [0.024]	0.23 [0.009]	
1/8	3.2 [0.126]	1.0 [0.039]	0.25 [0.010]	
1/4	6.4 [0.252]	1.6 [0.063]	0.30 [0.012]	
3/8	9.5 [0.374]	2.4 [0.095]	0.30 [0.012]	
1/2	12.7 [0.500]	3.7 [0.146]	0.38 [0.015]	
5/8	15.9 [0.626]	4.5 [0.177]	0.38 [0.015]	
3/4	19.0 [0.748]	5.7 [0.224]	0.38 [0.015]	
1	25.4 [1.000]	7.1 [0.230]	0.38 [0.015]	
1-1/4	32.0 [1.260]	8.8 [0.347]	0.38 [0.015]	

^{**}Wall thickness will be less if tubing recovery is restricted during shrinkage.

Ordering Information

Color	Standard Clear (-X)	
Size selection	Always order the largest size that will shrink snugly over the component to be covered. Special order sizes are available upon request.	
Standard packaging	In 1.2-meter [4-foot] lengths.	
Ordering description***	Specify product name, size and color (for example,TFE 22-X).	

^{***}Europe only. For supply to MIL spec., Def Stan and BS add -MS, -DS or -BS to ordering description.

Germany: 49-6251-133-1999 China: 86-400-820-6015 Japan: 81-44-844-8013 UK: 44-800-267-666