


SPECIFICATION

INPUT VOLTAGE: ±15VDC (NOMINAL)
INPUT CURRENT: ± 25 mA (NOMINAL)
ELECTRICAL STROKE: ±2.000[50.8]
SCALE FACTOR: 5V/ INCH [0.2 V/mm]
LINEARITY: ± 0.25% OF FULL RANGE MAX.
NULL VOLTAGE: 0.0 V DC
OUTPUT RIPPLE: 10 mV rms MAX.
STABILITY: 0.125% FULL SCALE
OUTPUT IMPEDANCE: LESS THAN 200 OHMS



REVISIONS

REV.	DESCRIPTION	DATE:	APPR.
A	REVISED FOR CLARITY	11/12/98	R.E.A.
B	11.71 +/- .03 WAS 11.21	12/2/96	R.E.A.
C	UPDATED TO LATER DRAWING PROGRAM	5/18/99	R.E.A.
D	REVISED PER ECR/ECON #284	12/12/00	R.E.A.
E	REVISED PER ECR/ECON #712	3/18/05	R.E.A.
E1	REDRAWN WITH NO CHANGES	09/28/20	



[] DENOTES MILLIMETER
◐ DENOTES CENTER OF CORE AT ELECTRICAL CENTER

MATING CONNECTOR SUPPLIED



MATERIAL:

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES		DRAFTSMAN:	DATE:
TOLERANCES ARE:		R.E.A.	1 AUG 95
ANGLES:		CHECKER:	DATE:
FRACTIONS:		DATE:	
DECIMAL:		APPROVED:	DATE:
XX= +/- .01		DATE:	
.XXX= +/- .005		APPROVED:	DATE:
FINISH:		APPROVED:	DATE:
TITLE		HSD 750 2000	
OUTLINE		C.A.G.E. No. 06VW0	
SCALE: NONE		DRAWING No. 020915070000	
SHEET No. 1 of 1			