



REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	-	-	-


**SPECIFICATIONS**

INPUT VOLTAGE:  $\pm 15$  V DC (NOM)  $\pm 25$  mA  
 ELECTRICAL STROKE:  $\pm 2.000$ "  
 LINEARITY: 0.25% OF FULL RANGE (MAX)  
 NULL VOLTAGE: 0V DC  
 RIPPLE:  $< 25$  mV rms  
 STABILITY: 0.125% FULL SCALE  
 OUTPUT IMPEDANCE:  $< 200$  OHMS  
 OPERATING TEMPERATURE: 0 TO 160 DEG. F  
 REPEATABILITY: 0.00002"  
 SHOCK SURVIVAL: 1000 g's, 11ms  
 VIBRATION (DC TO 2000 Hz): 50 g's rms  
 PRE TRAVEL: 0.02" (NOM)  
 OVER TRAVEL: 0.02" (NOM)

REVISIONS			
REV.	DESCRIPTION	DATE	APPR.



PT06-10-66 (5R) or equiv.  
 MATING CONNECTOR SUPPLIED



CHECK SPECIFIC DIMENSIONS PER TOLERANCES & FINISHES FOR TOLERANCES PER:		<b>Macro Sensors</b> the of Howard A. Roberts Technology, Inc.	
PART NO.: QTY:	DATE:	TITLE:	GHSDR 750 2000 OUTLINE
DRAWING NO.:	SCALE:	CAGE CODE:	032913050000
SHEET NO.:	1 of 1	SHEET NO.:	1 of 1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	-	TE Connectivity	
DIMENSIONS: INCHES		CHK	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	-	NAME: GHSDR 750 2000 OUTLINE	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC	-		
MATERIAL	FINISH	WEIGHT	-	SIZE	A2
CUSTOMER DRAWING		SCALE	NTS	CAGE CODE	00779
		SHEET	1 of 1	DRAWING NO.	032913050000
		RESTRICTED TO	-	SCALE	NTS