




ELECTRICAL	MECHANICAL	ENVIRONMENTAL	HOUSING	MATERIAL		FINISH
Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A, Fig. 310.2	Temperature Rating -65°C To +105°C	CAP	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303		GOLD PLATE PER MIL-G-45204
Frequency Range (GHz) DC to 18	Recommended Mating Torque N/A	Vibration MIL-STD-202, Method 204, Condition D	DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457		N/A
Volt Rating (VRMS MAX) @ Sea Level 335	Mating Characteristics:	Shock MIL-STD-202, Method 213, Condition I	CENTER CONTACT CONTACT EXT.	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H		GOLD PLATE PER MIL-G-45204
VSWR N/A	Insertion (MAX Lbs) 3.0	Thermal Shock MIL-STD-202, Method 107, Condition B Except High Temp Shall Be +125°C	COMPONENT	MATERIAL		FINISH
Insertion Loss (dB MAX) N/A	Withdrawal (MIN Oz) 1.0	Moisture Resistance MIL-STD-202, Method 106	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON	DRAWN BY DAN CASTRO 8/26/82	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599	
RF Leakage (dB MIN) N/A	Force to Engage and Disengage (In-Lbs MAX) 2.0	Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray	FRAC. DEC. ANGLES ± 1/64 ± .005 ± °	CHECKED BY GERALD SONIA 9/14/82		
Corona, 70,000 Ft (VRMS MIN) 250	Center Contact Captivation		These drawings and specifications are the property of M/A-COM Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	APPROD BY RMF 9/14/82	TITLE OSM PRINTED WIRING BOARD RIGHT ANGLE JACK RECEPTACLE M39012/94-3001	
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1,000	Axial (Lbs) 6.0		USE ASS'Y PROCEDURE			
Contact Resistance (Milliohms MAX)	Radial (In-Oz) 4.0				SIZE B	CODE IDENT NO. 26805
Center Contact 3.0	Cable Retention				SCALE 6 : 1	2064-8001-90
Outer Contact 2.0	Axial Force (Lbs) N/A					REV 040
Cable to Housing N/A	Torque (In-Oz) N/A					
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670	Weight (Grams) 3.1					
I.R.(Megohms MIN) 5,000						