






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
HB	—		E	REMOVED THE RIB ON BASE TO CASE ECO-15-011310	29-Sep-15	YS.H SM.C
			E1	ADD NEW PN ECO-19-017316	13-Nov-19	WQ.Y K.T



CONNECTION FIGURE




FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING
(BOTTOM VIEW)


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	Fu Bo	TE TE Connectivity		
		CHK				
DIMENSIONS: mm		APVD	CH,HSU	NAME		
		PRODUCT SPEC		T77*1D10-** CUSTOMER DRAWING		
		APPLICATION SPEC				
MATERIAL		WEIGHT		SIZE	CAGE CODE	DRAWING NO
				A3	00779	C= 1-1393194-9
		CUSTOMER DRAWING		SCALE	SHEET	REV
				5:1	1 of 2	E1

LOC	DIST	REVISIONS				
HB	—	P	LTR	DESCRIPTION	DATE	DWN
			—	SEE SHEET 1	—	—

107-84030	4-1393194-2	T77V1D10-12	T77V1D10-12	r
107-79010	3-1393194-8	T77V1D10-24-01	T77V1D10-24-01	q
107-79010	2-1393194-2	T77V1D10-48	T77V1D10-48	p
107-79010	2-1393194-1	T77V1D10-24	T77V1D10-24	o
107-79010	2-1393194-0	T77V1D10-18	T77V1D10-18	n
107-79010	1-1393194-9	T77V1D10-12	T77V1D10-12	m
107-79010	1440005-1	T77V1D10-09	T77V1D10-09	l
107-79010	8-1440009-1	T77V1D10-06	T77V1D10-06	k
107-79010	1-1393194-8	T77V1D10-05	T77V1D10-05	j
107-79010	1-1393194-7	T77V1D10-03	T77V1D10-03	i
107-79010	9-1440004-7	T77S1D10-48	T77S1D10-48	h
107-79010	1-1393194-0	T77S1D10-24	T77S1D10-24	g
107-79010	9-1440004-5	T77S1D10-18	T77S1D10-18	f
107-79010	1393194-9	T7S1D10-12	T77S1D10-12	e
107-79010	1393194-8	T77S1D10-09	T77S1D10-09	d
107-79010	9-1440004-2	T77S1D10-06	T77S1D10-06	c
107-79010	1393194-7	T77S1D10-05	T77S1D10-05	b
107-79010	1393194-6	T77S1D10-03	T77S1D10-03	a
PACKAGE SPEC.	PART NO	DESCRIPTION	PART A	TYPE

RELAY TYPE

NOTE
1.LOT NO SYSTEM AS FOLLOWING:



- 2.TERMINAL DIMENSION IS BEFORE SOLDER DIP;
3.FOR THE TIN-PLATING OF THE PINS:
+0.1mm FOR WIDTH,THICKENSS AND DIAMETER.
+0.5mm FOR LENGTH.
4.MARKING FROM INK TO LASER AND USING WELDED CONTACT

5.ADD LOT NO. SYSTEM AS FOLLOWING;



- I, DIGITS FOR DAY OF THE WEEK
1...MONDAY IN THIS WEEK;
2...TUESDAY IN THIS WEEK;
.....
7...SUNDAY IN THIS WEEK
II, DIGITS FOR SHIFT OF THE DAY
1...DAY SHIFT IN THIS DAY;
2...NIGHT SHIFT IN THIS DAY;
III, ONE CHARACTER DISTINGUISH THE LINE IDENTITY, SUCH AS: A,B,.....Z

		EPOXY RESIN	SEAL (BASE & BOBBIN)	15
		MW79	MAGNETIC WIRE	14
94V-0		P.B.T	CASE	13
94V-0		P.B.T	BASE	12
94VHB		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
94V-0		P.P.S	CARD	9
		Ag ALLOY	MOVABLE CONTACT	8
		Ag	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	CU ALLOY	NO.TERMINAL	5
	SOLDER DIP	CU ALLOY	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	Fu Bo	—
		CHK	Xiaoning.Zhang	—
		APVD	CH,HSU	—
DIMENSIONS: mm		PRODUCT SPEC	—	
		APPLICATION SPEC	—	
MATERIAL		WEIGHT	—	
FINISH		—		
		CUSTOMER DRAWING		

TE Connectivity

NAME

T77*1D10-** CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=

1-1393194-9

—

SCALE

SHEET

of

REV

5:1

2

2

E1