





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F1	REVISED PER PCN-24-200133	18MAR2024	RK	CB
	G	REVISED PER PCN-24-208998	21MAY2024	GB	DM
	G1	REVISED PER PCN-24-223984	14OCT2024	RK	CB
	G2	REVISED PER PCN-25-234736	06FEB2025	GB	DM


OPTIONAL TRACEABILITY ID
LOCATED ON DIAMETER



SECTION A-A
WIRE BARREL

SECTION B-B
INSULATION BARREL

TE INTERNAL PN	DEUTSCH PN	REV	PLATING
1062-20-0222	1062-20-0222	E	Ni/Cu overall
1062-20-0244	1062-20-0244	F	Selective Au, Ni overall, Sn/Ni Wire Barrel
1062-20-0277	1062-20-0277	E	Sn/Ni/Cu overall

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. APOSTOL 02DEC2009	TE Connectivity			
DIMENSIONS: INCHES[mm]		CHK D. MEYER 02DEC2009				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [0.64] 4 PLC ± ANGLES ±	APVD R. REED 03DEC2009	NAME PIN, STAMPED CONTACT SIZE 20 16-22 AWG, .050-.085 INS			
		PRODUCT SPEC 108-151000				
		MATERIAL 	FINISH SEE TABLE	APPLICATION SPEC 114-151003	SIZE A3	CAGE CODE 4AFU8
WEIGHT 0.21 g						
CUSTOMER DRAWING			SCALE 6:1	SHEET 1 OF 1	REV G2	