

REVISIONS							
REV	DESCRIPTION	DATE	APPROVED				
Α	REDRAWN	12-15-88	DAC				
01 ₁	REDRAWN IN CAD	BB 5-23-90	M.Y.				
012	VSWR: N/A WAS 335. RF LEAKAGE: 90 WAS 012.	CKM					
	CONT.RESIS., CTR & OUTER 4.0 WAS 2.0. FORCE	10-30-90	KCM				
	TO ENGAGE: 2 WAS 7, ECN 90-0701						

			HOUSING	STAINLESS		PASSIVATE PER	
ELECTRICAL	MECHANICAL	ENVIRONMENTAL	BUSHING	ASTM-A484		ASTM-A380	
Nominal Impedance (Ohms) 50 ±1	Interface Dimensions	Temperature Rating -55° to +125°C		A582, TYPE	. 505		
Frequency Range (GHz) DC to 50	See Catalogue	Vibration MIL-STD-202, Method	DIELECTRIC	TFE FLUORO	CARBON	N/A	
Volt Rating (VRMS MAX)	Mating Characteristics:	204, Condition D, 20Gs		PER ASTM-D			
© Sea Level N/A	Insertion (MAX Lbs) 2	Shock MIL-STD-202, Method 213,		MIL-P-1946			
VSWR DC to 18 GHz : 1.11MAX	Withdrawal (MIN Oz) 1	Condition I, 100Gs		FED. SPEC	L-P-403		
18 to 26.5 GHz : 1.13MAX	Force to Engage (In/Lbs MAX) 2	Thermal Shock MIL-STD-202,	CENTER CONTACT	BERYLLIUM	COPPER PER	GOLD PLATE PER	
26.5 to 50 GHz : 1.29MAX		Method 107, Condition B			ALLOY 173	MIL-G-45204 OVE	
Insertion Loss (dB_MAX) .07x\sqrt{f(GHz)}	ss (dB_MAX) .07x\sqrt{f(GHz)} Center Contact Captivation Moisture Resistance MIL-STD-202,				COPPER PLATE PEI		
RF Leakage (dB MIN) (Interface Only,	Axial (Lbs) 4	Method 106				MIL-C-14550	
Fully Mated)(90-f(GHz))		Corrosion - MIL-STD-202, Method	COMPONENT MA		RIAL	FINISH	
Carana, 70,000 Ft (VRMS MIN) 150		101, Condition B	LINI ESS OTHERWISE SPECIEED	1	(1) (2	1 11 11 11 11	
Dielectric Withstanding Voltage			DIMENSIONS ARE IN INCHES DAC	12-05-88	AMP II	ncorporated	
(VRMS MIN) 8 Sea Level 500			TOLERANCE ON OFFICE DAC	01–02–89	140 F	ourth Avenue	
Contact Resistance (Milliohms MAX)			± 1/64 ±.005 ± 1° S.M.	01–03–89	Waltho	am, MA 02451-7599	
Center Contact 4.0			These drawings and specifical-	USE ASSY PROCEDURE	TITLE		
Outer Contact 4.0			lone are the property of Omni Spectra incorporated and shall	COL AGO I I NOCEDORE	OS-50 JACK TO JACK ADAPTER		
RF High Potential 8 Sea Level			not be reproduced or capied or used in whole or in part as the		<u> </u>	REV	
(VRMS MIN 9 5 MHz) 600			basis for the manufacture or sale of item(s) without written	NO. A.P. N/A	SIZE CODE DENT NO. B 26805	8580-0000-02 01	
I.R.(Megohms MIN) 5000			permission.		scale 5:1	SHEET 1 0F 1	

CUSTOMER DRAWING

AMP PART # 1063380-1 SHEET 1 OF 1 REV A