


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HC	00		B	REVISED PER 0U20-0262-01	20FEB03	G.V.	JGH



NOTES:

- DESIGNED FOR USE WITH .085 DIA (RG 405/U) SEMI RIGID CABLE.
- CAPTURED CENTER CONTACT
- PICTORIAL VIEW IS AFTER CRIMPING
- MIN STRAIGHT CABLE LENGTH, .317
- IT IS SUGGESTED TO BEND CABLE PRIOR TO CRIMPING.

	DIM "A"
BEFORE CRIMPING	.787 REF (20.0mm)
AFTER CRIMPING	.667 (16.9mm)

CABLE ENTRY DIAMETER MINIMUM	
HOUSING	.088
CONTACT	.021

HOUSING MOUNTING NUT LOCKWASHER	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER QQ-P-35
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
O-RING	FLOUROSILICONE PER MIL-R-25988 CLASS I, TYPE I.	N/A
COMPONENT	MATERIAL	FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. VIERA 10FEB2003	 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES		CHK J.HAVENER 20FEB03	NAME OSP BULKHEAD FEEDTHROUGH CABLEPLUG REAR MOUNT COMPRESSION CRIMP ATTACHMENT			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. HAVENER 20FEB03				
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± 1°	PRODUCT SPEC —				
	—	APPLICATION SPEC —				
MATERIAL —	FINISH —	WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C=1081004	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 10:1	SHEET 1 OF 1	REV B	