

		5.08 [.200]	1	4	$\triangle 3$	$\triangle 8$	3-102398-5
	SUPERSEDED BY 1-102398-8	91.44 [3.600]	35	72	$\triangle 3$		3-102398-4
	SUPERSEDED BY 1-102398-3, -8	88.90 [3.500]	34	70	$\triangle 3$		3-102398-3
	SUPERSEDED BY 1-102398-5	86.36 [3.400]	33	68	$\triangle 3$		3-102398-2
	SUPERSEDED BY 1-102398-5	83.82 [3.300]	32	66	$\triangle 3$		3-102398-1
		81.28 [3.200]	31	64	$\triangle 3$	$\triangle 8$	3-102398-0
	SUPERSEDED BY 1-102398-3	78.74 [3.100]	30	62	$\triangle 3$		2-102398-9
		76.20 [3.000]	29	60	$\triangle 3$		2-102398-8
	SUPERSEDED BY 1-102398-2, -3	73.66 [2.900]	28	58	$\triangle 3$		2-102398-7
		71.12 [2.800]	27	56	$\triangle 3$	$\triangle 8$	2-102398-6
	OBSOLETE	68.58 [2.700]	26	54	$\triangle 3$		2-102398-5
	SUPERSEDED BY 1-102398-1	66.04 [2.600]	25	52	$\triangle 3$		2-102398-4
		63.50 [2.500]	24	50	$\triangle 3$		2-102398-3
	SUPERSEDED BY 1-102398-0	60.96 [2.400]	23	48	$\triangle 3$		2-102398-2
	SUPERSEDED BY 1-102398-0	58.42 [2.300]	22	46	$\triangle 3$		2-102398-1
		55.88 [2.200]	21	44	$\triangle 3$	$\triangle 8$	2-102398-0
	SUPERSEDED BY 102398-8	53.34 [2.100]	20	42	$\triangle 3$		1-102398-9
		50.80 [2.000]	19	40	$\triangle 3$		1-102398-8
	SUPERSEDED BY 1-102398-8, -7	48.26 [1.900]	18	38	$\triangle 3$		1-102398-7
	SUPERSEDED BY 1-102398-5, -7	45.72 [1.800]	17	36	$\triangle 3$		1-102398-6
		43.18 [1.700]	16	34	$\triangle 3$		1-102398-5
	OBSOLETE	40.64 [1.600]	15	32	$\triangle 3$		1-102398-4
		38.10 [1.500]	14	30	$\triangle 3$		1-102398-3
		35.56 [1.400]	13	28	$\triangle 3$	$\triangle 8$	1-102398-2
		33.02 [1.300]	12	26	$\triangle 3$		1-102398-1
		30.48 [1.200]	11	24	$\triangle 3$		1-102398-0
	OBSOLETE	27.94 [1.100]	10	22	$\triangle 3$		1-102398-9
		25.40 [1.000]	9	20	$\triangle 3$		102398-8
		22.86 [.900]	8	18	$\triangle 3$		102398-7
		20.32 [.800]	7	16	$\triangle 3$		102398-6
		17.78 [.700]	6	14	$\triangle 3$		102398-5
		15.24 [.600]	5	12	$\triangle 3$		102398-4
		12.70 [.500]	4	10	$\triangle 3$		102398-3
		10.16 [.400]	3	8	$\triangle 3$		102398-2
		7.62 [.300]	2	6	$\triangle 3$		102398-1
		B	A	NO OF POSN	FINISH		PART NO.

81.28 [3.200]	31	64		8-102398-0
76.20 [3.000]	29	60		7-102398-8
68.58 [2.700]	26	54		8-7-102398-5
63.50 [2.500]	24	50		7-102398-3
50.80 [2.000]	19	40		6-102398-8
43.18 [1.700]	16	34		6-102398-5
40.64 [1.600]	15	32		8-6-102398-4
38.10 [1.500]	14	30		6-102398-3
35.56 [1.400]	13	28		8-6-102398-2
33.02 [1.300]	12	26		6-102398-1
30.48 [1.200]	11	24		6-102398-0
27.94 [1.100]	10	22		8-5-102398-9
25.40 [1.000]	9	20		5-102398-8
22.86 [.900]	8	18		5-102398-7
20.32 [.800]	7	16		5-102398-6
17.78 [.700]	6	14		5-102398-5
15.24 [.600]	5	12		5-102398-4
12.70 [.500]	4	10		5-102398-3
10.16 [.400]	3	8		5-102398-2
7.62 [.300]	2	6		5-102398-1
B	A	NO OF POSN	FINISH	PART NO

