


			REVISIONS																																																																																						
			REV	DESCRIPTION	DATE	APPROVED																																																																																			
			01	0 RELEASED	DAC 3/9/99	 3/9/99																																																																																			
<table><thead><tr><th>ELECTRICAL</th><th>MECHANICAL</th><th>ENVIRONMENTAL</th></tr></thead><tbody><tr><td>Nominal Impedance (Ohms) 50</td><td>Interface Dimensions</td><td>Temperature Rating -65°C to +165°C</td></tr><tr><td>Frequency Range (GHz) DC to 18</td><td>OSP: SEE CATALOG</td><td>Vibration MIL-STD-202, Method 204, Condition D.</td></tr><tr><td>Volt Rating (VRMS MAX)</td><td>OSM: MIL-STD-348A FIG 310.1</td><td>Shock MIL-STD-202, Method 213, Condition I.</td></tr><tr><td>VSWR 1.05 +.005 f(GHz)</td><td>Recommended Mating</td><td>Thermal Shock MIL-STD-202, Method 107, Condition C.</td></tr><tr><td>Insertion Loss (dB MAX) .06 √f(GHz)</td><td>Torque 7 - 10 in-lbs</td><td>Moisture Resistance MIL-STD-202, Method 106</td></tr><tr><td>RF Leakage (dB MIN) -60 @ 2-3(GHz)</td><td>Mating Characteristics:</td><td>Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray</td></tr><tr><td>Corona, 70,000 Ft (VRMS MIN) 250</td><td>Insertion (MAX Lbs) N/A</td><td></td></tr><tr><td>Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1,500</td><td>Withdrawal (MIN Oz) N/A</td><td></td></tr><tr><td>Contact Resistance (Milliohms MAX)</td><td>Force to Engage</td><td></td></tr><tr><td>Center Contact 4.0</td><td>OSP END: (Lbs MAX) 3.0</td><td></td></tr><tr><td>Outer Contact 2.0</td><td>OSM END: (In-Lbs MAX) 2.0</td><td></td></tr><tr><td>Cable to Housing N/A</td><td>Force to Disengage</td><td></td></tr><tr><td>RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670</td><td>OSP END: (Lbs MAX) 1.5</td><td></td></tr><tr><td>I.R.(Megohms MIN) 5,000</td><td>OSM END: (In-Lbs MAX) 2.0</td><td></td></tr><tr><td></td><td>Center Contact Captivation</td><td></td></tr><tr><td></td><td>Axial (Lbs) 6.0</td><td></td></tr><tr><td></td><td>Radial (In-Oz) N/A</td><td></td></tr><tr><td></td><td>Cable Retention</td><td></td></tr><tr><td></td><td>Axial Force (Lbs) N/A</td><td></td></tr><tr><td></td><td>Torque (In-Oz) N/A</td><td></td></tr><tr><td></td><td>Weight (Grams) TBD</td><td></td></tr></tbody></table>			ELECTRICAL	MECHANICAL	ENVIRONMENTAL	Nominal Impedance (Ohms) 50	Interface Dimensions	Temperature Rating -65°C to +165°C	Frequency Range (GHz) DC to 18	OSP: SEE CATALOG	Vibration MIL-STD-202, Method 204, Condition D.	Volt Rating (VRMS MAX)	OSM: MIL-STD-348A FIG 310.1	Shock MIL-STD-202, Method 213, Condition I.	VSWR 1.05 +.005 f(GHz)	Recommended Mating	Thermal Shock MIL-STD-202, Method 107, Condition C.	Insertion Loss (dB MAX) .06 √f(GHz)	Torque 7 - 10 in-lbs	Moisture Resistance MIL-STD-202, Method 106	RF Leakage (dB MIN) -60 @ 2-3(GHz)	Mating Characteristics:	Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray	Corona, 70,000 Ft (VRMS MIN) 250	Insertion (MAX Lbs) N/A		Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1,500	Withdrawal (MIN Oz) N/A		Contact Resistance (Milliohms MAX)	Force to Engage		Center Contact 4.0	OSP END: (Lbs MAX) 3.0		Outer Contact 2.0	OSM END: (In-Lbs MAX) 2.0		Cable to Housing N/A	Force to Disengage		RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670	OSP END: (Lbs MAX) 1.5		I.R.(Megohms MIN) 5,000	OSM END: (In-Lbs MAX) 2.0			Center Contact Captivation			Axial (Lbs) 6.0			Radial (In-Oz) N/A			Cable Retention			Axial Force (Lbs) N/A			Torque (In-Oz) N/A			Weight (Grams) TBD		<table><thead><tr><th>COMPONENT</th><th>MATERIAL</th><th>FINISH</th></tr></thead><tbody><tr><td>HOUSING COUPLING NUT</td><td>STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303</td><td>PASSIVATE PER QQ-P-35</td></tr><tr><td>DIELECTRIC</td><td>PTFE FLUOROCARBON PER ASTM-D-1457</td><td>N/A</td></tr><tr><td>CENTER CONTACT</td><td>BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H</td><td>GOLD PLATE PER MIL-G-45204</td></tr><tr><td>RETAINING RING</td><td>BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H</td><td>N/A</td></tr><tr><td>GASKET</td><td>FLUOROCARBON RUBBER PER MIL-R-83248 TYP 1 CLASS 1</td><td>N/A</td></tr></tbody></table>			COMPONENT	MATERIAL	FINISH	HOUSING COUPLING NUT	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER QQ-P-35	DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A	CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204	RETAINING RING	BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H	N/A	GASKET	FLUOROCARBON RUBBER PER MIL-R-83248 TYP 1 CLASS 1	N/A
ELECTRICAL	MECHANICAL	ENVIRONMENTAL																																																																																							
Nominal Impedance (Ohms) 50	Interface Dimensions	Temperature Rating -65°C to +165°C																																																																																							
Frequency Range (GHz) DC to 18	OSP: SEE CATALOG	Vibration MIL-STD-202, Method 204, Condition D.																																																																																							
Volt Rating (VRMS MAX)	OSM: MIL-STD-348A FIG 310.1	Shock MIL-STD-202, Method 213, Condition I.																																																																																							
VSWR 1.05 +.005 f(GHz)	Recommended Mating	Thermal Shock MIL-STD-202, Method 107, Condition C.																																																																																							
Insertion Loss (dB MAX) .06 √f(GHz)	Torque 7 - 10 in-lbs	Moisture Resistance MIL-STD-202, Method 106																																																																																							
RF Leakage (dB MIN) -60 @ 2-3(GHz)	Mating Characteristics:	Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray																																																																																							
Corona, 70,000 Ft (VRMS MIN) 250	Insertion (MAX Lbs) N/A																																																																																								
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1,500	Withdrawal (MIN Oz) N/A																																																																																								
Contact Resistance (Milliohms MAX)	Force to Engage																																																																																								
Center Contact 4.0	OSP END: (Lbs MAX) 3.0																																																																																								
Outer Contact 2.0	OSM END: (In-Lbs MAX) 2.0																																																																																								
Cable to Housing N/A	Force to Disengage																																																																																								
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670	OSP END: (Lbs MAX) 1.5																																																																																								
I.R.(Megohms MIN) 5,000	OSM END: (In-Lbs MAX) 2.0																																																																																								
	Center Contact Captivation																																																																																								
	Axial (Lbs) 6.0																																																																																								
	Radial (In-Oz) N/A																																																																																								
	Cable Retention																																																																																								
	Axial Force (Lbs) N/A																																																																																								
	Torque (In-Oz) N/A																																																																																								
	Weight (Grams) TBD																																																																																								
COMPONENT	MATERIAL	FINISH																																																																																							
HOUSING COUPLING NUT	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER QQ-P-35																																																																																							
DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A																																																																																							
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204																																																																																							
RETAINING RING	BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H	N/A																																																																																							
GASKET	FLUOROCARBON RUBBER PER MIL-R-83248 TYP 1 CLASS 1	N/A																																																																																							
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON <table><thead><tr><th>FRAC.</th><th>DEC.</th><th>ANGLES</th></tr></thead><tbody><tr><td>± 1/64</td><td>±.005</td><td>± 1°</td></tr></tbody></table> These drawings and specifications are the property of AMP Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.			FRAC.	DEC.	ANGLES	± 1/64	±.005	± 1°	DRAWN BY DAC 3/9/99			AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599																																																																													
			FRAC.	DEC.	ANGLES																																																																																				
			± 1/64	±.005	± 1°																																																																																				
CHECKED BY		APPROVED BY  3/9/99																																																																																							
USE ASS'Y PROCEDURE		NO. AP. N/A		TITLE OSM PLUG TO OSP PLUG ADAPTER																																																																																					
SIZE B		CODE IDENT NO. 26805		4581-5002-02		REV 01																																																																																			
SCALE 5:1				SHEET 1 OF 1																																																																																					