SAFETY ORGANIZATIONS

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

UL RECOGNIZED: UL 1283 CSA CERTIFIED: CSA C22.2 No. 8 VDE APPROVED: EN 60939-2

OPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 10 AMP, 120/250 VAC,

10 AMP/40°C, 250 VAC

LINE FREQUENCY: 50-60Hz

MAXIMUM LEAKAGE CURRENT,

EACH LINE TO GROUND: 0.22mA @ 120V 60Hz

0.38mA @ 250V 50Hz

OPERATING AMBIENT TEMP. RANGE: -10°C TO +40°C @ RATED CURRENT, Ir. IN AN AMBIENT, T_0 , HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT, I_0 , IS AS FOLLOWS: $I_1 = I_2 - I_3 - I_4 - I_5 - I_5 - I_6$ 85 - Tα $I_0 = I_r -$

RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: -40°C TO +85°C HUMIDITY: 21 DAYS @ 40°C 95% RH. CURRENT OVERLOAD TEST: 6 TIMES In FOR 8 SECONDS

CUSTOMER DRAWING CATALOG # 10EJS8 ECN # APPRVD. DATE 24-261887 JB 16JAN24

TEST SPECIFICATIONS:

INDUCTANCE: 0.35 mH NOMINAL CAPACITANCE: (MEASURED @ 1KHz, 0.250VAC MAX., 25°C±1°C)

0.0059 μF±20% 0.1015 μF±20% LINE TO GROUND: LINE TO LINE:

DISCHARGE RESISTOR: 1.5 M ∩

L/G AND L/L I.R.

NO DISCHARGE RESISTOR: 6000M ← (MIN.) @ 100VDC.

20°C AND 50% RH


RECOMMENDED RECEIVING INSPECTION HIPOT:

LINE TO GROUND: 1500 VAC OR 2250 VDC FOR 1 MINUTE

LINE TO LINE: 1450 VDC FOR 1 MINUTE

FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



				/ 1 / 1		11.1.3	THOS	O.T.T.D.					PARTS SHALL COMPL
I	50 A - 50 A (MINIMUM) INSERTION LOSS												
FREQUENCY MHz	.05	0.1	.15	0.5	1	5	10	30	/	/	/	/	UNLESS DTHERWI TDLERANCE TO E MATERIAL & FIN
COMMON dB	1	4	7	14	18	31	36	51	/	/	/	/	NOTES:
DIFF. dB	-	5	8	17	21	23	36	38	/	/	/	/	
SHEET SIZE	THIRD A	WGLE PRO	2	THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION.									
<u> </u>					com)	10EJ\$8-C.ckd							

PARTS SHALL COMPLY WITH TYCO ELECTRONIC	S 138-702 SPECIFICATION FOR HAZARDOUS SUBSTANCES
UNLESS DTHERWISE SPECIFIED TOLERANCE TO BE ±0.025 MATERIAL & FINISH: AS SUPPLIED DIMENSIONS IN INCHES	ETE TE Connectivity
NOTES:	POWER LINE FILTER
	TE PART ND.: 4-6609006-1

NTS

DRAWING NUMBER:

10EJS8

 \mathbb{C}

09DEC04

SCALE: