



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		D	REVISED PER EC 0G3C-0205-05	07FEB06	GS	MM
			D1	REVISED PER ECO-09-020932	01SEP09	KK	AEG



- 1 GOLD PL. .000001 MIN. THK.
- 2 GOLD PL. .000015 MIN. THK.
- 3. PLATING IS NOT REQUIRED ON CARRIER STRIP
- 4 POST DIAGONAL .0315/.0345
- 5 NICKEL PL. .000050 MIN. THK.
- 6 GOLD PL. .000030 MIN. THK.
- 7 SOLDER PL. .000100 MIN. THK.
- 8 MATTE TIN PL. .000100 MIN. THK.
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	-	.965	.088	.702	1 5 8	10,000	6-118778-5
	-	.965	.088	.702	1 5 8	10,000	6-118778-4
9	OBSOLETE	-	.965	.088	.702	5 6 8	6-118778-2
	-	.965	.088	.702	1 5 6	10,000	1-118778-5
	-	.965	.088	.702	1 5 6	10,000	1-118778-4
9	OBSOLETE	-	.965	.088	.702	5 6 7	1-118778-2
	-	1.192	.088	.475	UNPLATED	10,000	1-118778-1
	OBSOLETE	119643	1.192	.088	.702	5 6 7	1-118778-0
	-	1.192	.088	.702	1 5 6	10,000	118778-9
9	OBSOLETE	-	1.192	.088	.702	1 2 5	118778-6

COMB NO.		A	W	P	FINISH		QUANTITY/REEL		PART NO.							
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	—											
				CHK	—											
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME											
INCHES				—	CONTACT, ECONOMATE I											
		0 PLC ± —		PRODUCT SPEC	(.156 x .200 CL)											
		1 PLC ± —		—												
		2 PLC ± —														
		3 PLC ± .005		APPLICATION SPEC												
		4 PLC ± —		—												
ANGLES ± 0°30'				—	SIZE	CAGE CODE	DRAWING NO			RESTRICTED TO						
MATERIAL		FINISH		WEIGHT	A2 00779			C=118778			—					
COPPER ALLOY 110 172 QQ-C-533				Au PL./MIL-G-45204 Ni PL./QQ-N-290				SCALE		5:1		SHEET	1 OF 1		REV	D1
CUSTOMER DRAWING																