

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	N/A ,N/A .
© COPYRIGHT N/A BY TYCO ELECTRONICS CORPORATION.	ALL RIGHTS RESERVED.	


LOC	DIST	REVISIONS					
DF	XO	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REV PER 0G3D-0032-03	11-03	JMK	JL

COMPONENT	MATERIAL	FINISH
HOUSING — CLAMP NUT	STAINLESS STEEL PER ASTM-A-484 OR ASTM-A-582 TYPE 303	PASSIVATED PER ASTM-A-380 —
— DIELECTRIC —	PTFE FLUORCARBON PER ASTM-D-1457 —	— — —
— INNER SLEEVE —	BRASS PER ASTM-B-16 HALF HARD —	GOLD PLATED PER ASTM-B-488 —
— CENTER CONTACT —	BERYLLIUM COPPER PER ASTM-B-194 ALLOY C17200, CONDITION H	GOLD PLATED PER ASTM-B-488 —
— — —	— — —	— — —
— — —	— — —	— — —
— — —	— — —	— — —
— — —	— — —	— — —


ENVIRONMENTAL
TEMPERATURE RATING: -65°C TO +165°C
VIBRATION: MIL-STD-202, METHOD 204, CONDITION D
SHOCK: MIL-STD-202, METHOD 213, CONDITION 1
MOISTURE RESISTANCE: MIL-STD-202, METHOD 106
CORROSION: MIL-STD-202, METHOD 101, CONDITION B. 5% SALT SPRAY
THERMAL SHOCK: MIL-STD-202, METHOD 107, CONDITION B EXCEPT HIGH TEMP 115°C

MECHANICAL		
INTERFACE DIMENSIONS: MIL-STD-348A FIG.	310.2	
RECOMMENDED MATING TORQUE: 7-10 IN-LBS		
FORCE TO ENGAGE & DISENGAGE (IN-LBS MAX:)	2.0	
WEIGHT (GRAMS):	TBD	
MATING CHARACTERISTICS:	INSERTION (MAX LBS)	2
	WITHDRAWAL (MIN OZ):	1
CABLE RETENTION:	AXIAL FORCE (LBS)	30 MIN
	TORQUE (IN-OZ):	16.0
CENTER CONTACT CAPTIVATION:	AXIAL (LBS):	6.0
	RADIAL (IN-OZ):	N/A

ELECTRICAL	
NORMAL IMPEDANCE (OHMS):	50
FREQUENCY RANGE (GHz):	DC TO 18
VOLT RATING @ SEA LEVEL (VRMS MAX):	335
VSWR:	1.07+0.01f(GHz)
INSERTION LOSS: (dB MAX):	.03 $\sqrt{f(\text{GHz})}$
RF LEAKAGE (dB MIN):	-90 @ 2-3 GHz
CORONA 70,000 FT (VRMS MIN):	250
DIELECTRIC WITHSTANDING VOLTAGE (VRMS MIN) AT SEA LEVEL:	1000
I.R. (MEGOHMS MIN):	5,000
RF HIGH POTENTIAL AT SEA LEVEL (VRMS MIN @ 5 MHz):	670
CONTACT RESISTANCE (MILLIOHMS MAX):	CENTER CONTACT: OUTER CONTACT: CABLE TO HOUSING: 3.0 2.0 0.5



AS SHIPPED TO CUSTOMER



ASSEMBLED VIEW

DESIGNED TO USE RG-405/U OR EQUIVALENT	
CABLE ENTRY DIAMETER MIN	
HOUSING:	N/A
CONTACT:	.024 [0.61]
CLAMP NUT:	N/A
SLEEVE:	.087 [2.21]
—	—

THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS: INCHES [mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:
		0 PLC ± -
		1 PLC ± -
		2 PLC ± -
		3 PLC ± .005 [0.13]
		4 PLC ± -
ANGLES		± -
MATERIAL		FINISH
SEE TABLE		SEE TABLE

DWN	10/10/02
J. KAISER	
CHK	11-20-02
J. LIPPERT	
APVD	11-20-02
J. LIPPERT	
PRODUCT SPEC	
—	
APPLICATION SPEC	
408-8752	
WEIGHT	TBD
CUSTOMER DRAWING	

		Tyco Electronics Corporation			
		Harrisburg, PA 17105			
NAME					
SMA FLANGE MOUNT CABLE JACK-SOLDER CLAMP ATTACHMENT (M39012/82-3007) CAT E					
-					
SIZE	CAGE CODE	DRAWING NO			RESTRICTED TO
A2	00779	C-1051093			-
		SCALE	5:1	SHEET	1 OF 1
					REV A