



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		B1	ECR-15-005665	10AUG2015	BDA	PKS

D


C

B

A



- CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 8.38 $\pm$ 0.08 [.330 $\pm$.003] CENTERS
- SLOT TERMINATES A SINGLE MAGNET WIRE ONLY. COPPER RANGE: 1.09-1.29mm [#17.5-#16] AWG. ALUMINUM RANGE: 1.22-1.45mm [#16.5-#15.0] AWG. ALUMINUM WIRE RANGE APPLIES FOR POST-TIN PLATED VERSIONS ONLY.
- AFTER INSERTION INTO PLASTIC HOLDER TAB PORTION MUST BE BENT OVER 45° TO 90° TO POTTED-IN TO PREVENT PULL-OUT WHEN MATING RECEPTACLE IS DISCONNECTED.
- VARNISH RESIST OVER 0.002032 [.000080] MIN TIN
- PRELIMINARY - NOT FOR PRODUCTION



4	5
0.002032 [.000080] MIN TIN	1217075-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MICHAEL S. FEHER 25MAR98	TE Connectivity			
DIMENSIONS: mm		CHK JEFF R. RUTH 25MAR98				
		APVD DENNY SCHWENK 25MAR98	NAME TAB, 4.75[.187] FASTON, MAG-MATE			
		PRODUCT SPEC 108-2012	SIZE A2			
MATERIAL H03 BRASS		APPLICATION SPEC 114-2066	CAGE CODE 00779			
FINISH SEE TABLE		WEIGHT -	DRAWING NO 1217075			
		CUSTOMER DRAWING	RESTRICTED TO -			
		SCALE 6:1	SHEET 1 OF 1			
			REV B1			