

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	N/A , N/A .
© COPYRIGHT N/A BY TYCO ELECTRONICS CORPORATION.	ALL RIGHTS RESERVED.	


COMPONENT	MATERIAL	FINISH
HOUSING —	STAINLESS STEEL PER ASTM-A-484 OR ASTM-A-582 TYPE 303	PASSIVATED PER ASTM-A-380 —
— DIELECTRIC —	PTFE FLUORCARBON PER ASTM-D-1457 —	— — —
— CENTER CONTACT —	BERYLLIUM COPPER PER ASTM-B-196 OR 197 ALLOY C17300, CONDITION H	GOLD PLATED PER ASTM-B-488 —
— — —	— — —	— — —
— — —	— — —	— — —
— FERRULE —	COPPER OR BRASS ALLOY, ROCKWELL F65 MAX	GOLD PLATED PER ASTM-B-488 —
— — —	— — —	— — —
— — —	— — —	— — —

ENVIRONMENTAL
TEMPERATURE RATING: -65°C TO +165°C
VIBRATION: MIL-STD-202, METHOD 204, CONDITION D
SHOCK: MIL-STD-202, METHOD 213, CONDITION 1
MOISTURE RESISTANCE: MIL-STD-202, METHOD 106
CORROSION: MIL-STD-202, METHOD 101, CONDITION B. 5% SALT SPRAY
THERMAL SHOCK: MIL-STD-202, METHOD 107, CONDITION B EXCEPT HIGH TEMP 85°C


MECHANICAL		
INTERFACE DIMENSIONS:	MIL-STD-348A FIG.	310.2
RECOMMENDED MATING TORQUE:	7-10 IN-LBS	
FORCE TO ENGAGE & DISENGAGE (IN-LBS MAX:)	2.0	
WEIGHT (GRAMS):	TBD	
MATING CHARACTERISTICS:	INSERTION (MAX LBS)	2
	WITHDRAWAL (MIN OZ):	1
CABLE RETENTION:	AXIAL FORCE (LBS)	30
	TORQUE (IN-OZ):	N/A
CENTER CONTACT CAPTIVATION:	AXIAL (LBS):	6.0
	RADIAL (IN-OZ):	N/A

ELECTRICAL	
NORMAL IMPEDANCE (OHMS):	50
FREQUENCY RANGE (GHz):	DC TO 12.4
VOLT RATING @ SEA LEVEL (VRMS MAX):	250
VSWR:	1.15+0.02f(GHz)
INSERTION LOSS: (dB MAX):	.06 $\sqrt{f(\text{GHz})}$
RF LEAKAGE (dB MIN):	-60 @ 2-3GHz
CORONA 70,000 FT (VRMS MIN):	190
DIELECTRIC WITHSTANDING VOLTAGE (VRMS MIN) AT SEA LEVEL:	750
I.R. (MEGOHMS MIN):	5000
RF HIGH POTENTIAL AT SEA LEVEL (VRMS MIN @ 5 MHz):	500
CONTACT RESISTANCE (MILLIOHMS MAX):	
	CENTER CONTACT: 3.0
	OUTER CONTACT: 2.0
	CABLE TO HOUSING: 0.5

LOC	DIST	REVISIONS					
DF	X0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REV PER 0G3D-0032-03	11-03	JMK	JL




AS SHIPPED TO CUSTOMER



ASSEMBLED VIEW

DESIGNED TO USE RG-122/U OR EQUIVALENT	
CABLE ENTRY DIAMETER MIN	
HOUSING:	.099 [2.51]
CONTACT:	.033 [0.84]
DIELECTRIC:	N/A
—	—
FERRULE:	.172 [4.37]

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: INCHES [mm]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 [0.13] 4 PLC ± - ANGLES ± ±
MATERIAL	FINISH
SEE TABLE	SEE TABLE

DWN	9/11/02
J. KAISER	
CHK	10-8-02
J. LIPPERT	
APVD	10-8-02
J. LIPPERT	
PRODUCT SPEC	
—	
APPLICATION SPEC	
408-8744	
WEIGHT	TBD
CUSTOMER DRAWING	

		Tyco Electronics Corporation Harrisburg, PA 17105	
NAME SMA STRAIGHT CABLE JACK-CRIMP ATTACHMENT (M39012/57B3020) CAT B —			
SIZE A2	CAGE CODE 00779	DRAWING NO C-1051913	RESTRICTED TO —
SCALE 5:1		SHEET 1 OF 1	REV A