SAFETY ORGANIZATIONS

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

UL RECOGNIZED: UL 1283 CSA CERTIFIED: CSA C22.2 No. 8 VDE APPROVED: EN 60939-2

OPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 130 AMP 277 VAC LINE TO GROUND

AND 480VAC PHASE TO PHASE

50

LINE FREQUENCY:

MAXIMUM LEAKAGE CURRENT.

@ 277VAC 50 HZ EACH LINE TO GROUND: 82 mA

OPERATING AMBIENT TEMP. RANGE: -10°C TO +50°C @ RATED CURRENT, In. IN AN AMBIENT, T_0 , HIGHER THAN 50°C, THE MAXIMUM OPERATING CURRENT, I_0 , IS AS FOLLOWS: $I_1 = I_1 - I_2 - I_3 = I_4 - I_4 - I_5 = I_5 - I_5 = I$ $I_0 = I_r$ <u> 100 - Ta</u>

RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: -40°C TO +85°C HUMIDITY: 21 DAYS @ 50°C 95% RH.
CURRENT OVERLOAD TEST: 6 TIMES Ir FOR 8 SECONDS

CUSTOMER DRAWING CATALOG # 130BCF10R APPRVD DATE ECN# 15-0153<u>24</u> 200CT15 HS

TEST SPECIFICATIONS:

INDUCTANCE: .55 mH NOMINAL CAPACITANCE: (MEASURED @ 1KHz, 0.250VAC MAX., 25°C±1°C)

LINE TO GROUND: . 94 μF±20% LINE TO LINE: 6.6 μF±20%


DISCHARGE RESISTOR: 2x1.5 / .66 M \(\text{L/G} \) AND L/L I.R. NO DISCHARGE RESISTOR: 6000M₁ (MIN.) 100VDC, 20°C AND 50% RH@

RECOMMENDED RECEIVING INSPECTION HIPOT:

1850 VDC FOR 1 MINUTE LINE TO LINE: 1850 VDC FOR 1 MINUTE

FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



50 A - 50 A (TYPICAL) INSERTION LOSS												
FREQUENCY MHz	.01	.03	.05	.10	.15	.30	.50	1.0	3.0	5.0	10	30
COMMON dB	6	22	31	43	52	72	80	63	45	37	26	9
DIFF. dB	27	37	40	38	53	75	80	64	54	50	47	30
SHEET SIZE	THIRD A	NGLE PRIL	5)	THIS INFORMATION IS COMFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCUSSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION.								

UNLESS OTHERWISE SPECIFIED
TOLERANCE TO BE ±0.64 (±0.025)
MATERIAL & FINISH: AS SUPPLIED
DIMENSIONS IN MM (INCHES) NOTES:

130BCF10R-A.ckd

TE Connectivity

A

CUSTOMER DRAWING

TE PART ND.: 2-1609989-7 DRAWING NUMBER

NTS 300CT15 130BCF10R