


WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ("EAR") PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 4801, ET SEQ.).

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REV PER ECN-24-275448	11JUL2024	LP	JG



1. FOR USE WITH KX23 & RG400U

SHELLS	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
DIELECTRICS	PTFE FLOUROCARBON PER ASTM-D-1457	N/A
GASKETS	SILICONE RUBBER PER A-A-59588	N/A
CONTACT	BeCu PER ASTM B196	GOLD PLATE PER ASTM B488 OVER NICKEL PLATE PER SAE-AMS-QQ-N-290
CRIMP FERRULE	COPPER OR BRASS ALLOY ROCKWELL B 45 MAX	SILVER PLATE PER ASTM B700
COMPONENT	MATERIAL	FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±0.3
	1 PLC ±0.3
	2 PLC ±0.3
	3 PLC ±0.3
	4 PLC ±0.3
	ANGLES ±5°
MATERIAL	FINISH
-	-
-	-

DWN	L. PROSPER	10JUL2024
CHK	J. GUNDERMANN	10JUL2024
APVD	D. WILSON	10JUL2024
PRODUCT SPEC	-	
APPLICATION SPEC	408-1799	
WEIGHT	-	
CUSTOMER DRAWING		

69814	69710-1	131233-1
DIE SET	CRIMP TOOL	PART NUMBER
NAME BNC JACK, 4 HOLE FLANGE MOUNT ASSEMBLY		
SIZE	CAGE CODE	DRAWING NO
A3	00779	C-131233
SCALE 3:1		SHEET 1 OF 1
REV B		RESTRICTED TO