


P	LTR	DESCRIPTION	DATE	DWN	APVD
	N	REVISED PER ECN-25-326854	13JUN2025	SP	PD




1 WIRE INSULATION: 10.8[.425]-11.9[.469]

2 WIRE CMA: 83700 to 119500


3 THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.

4. SEE TE CONNECTIVITY INSTRUCTION SHEET 408-2281 FOR TOOLING AND CRIMP INSTRUCTIONS, FIGURE 2 FOR WIRE STRIPPING DETAIL.




WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ("EAR") PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 4801, ET SEQ.).

56 grams	8.34±0.13 [.328±.005]	5/16 or M8	BODY: COPPER ASTM B187 ANNEALED TIN PLATE .00381[.000150] MIN THICK PER ASTM B 545 INSERT&FUNNEL:BRASS ASTM B36 NICKEL PLATE SAE AMS QQ-N-290A, DATED JULY 2000,.00254 [.000100] MIN THICK	134452-1
WEIGHT	DIM A	B	MATERIAL&FINISH	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JJ. DESPRETZ 23JUN2004	TE Connectivity		
DIMENSIONS: mm [Inches]		CHK G-ROBERT 23JUN2004			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Y. PETRONIN 23JUN2004	NAME SEALED COPALUM ASSEMBLY, 1/0, ALU		
MATERIAL TABLE		PRODUCT SPEC	-		
FINISH TABLE		APPLICATION SPEC	-		
-		WEIGHT	-		
-		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 2	REV N



P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

1 WIRE INSULATION: 10.8[.425]-.11.9[.469]

2 WIRE CMA: 83700 to 119500

3 THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.

4. SEE TE CONNECTIVITY INSTRUCTION SHEET 408-2281 FOR TOOLING AND CRIMP INSTRUCTIONS, FIGURE 2 FOR WIRE STRIPPING DETAIL.

WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ("EAR") PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 4801, ET SEQ.).

57 GRAMS	6.73±0.13 [.265±.005]	1/4 or M6	BODY: COPPER ASTM B187 ANNEALED TIN PLATE .00381[.000150] MIN THICK PER ASTM B 545	134452-3
56 GRAMS	8.34±0.13 [.328±.005]	5/16 or M8	INSERT&FUNNEL:BRASS ASTM B36 NICKEL PLATE SAE AMS QQ-N-290A, DATED JULY 2000,.00254 [.000100] MIN THICK	134452-2
WEIGHT	DIM A	B	MATERIAL&FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN JJ. DESPRETZ 23JUN2004

CHK G-ROBERT 23JUN2004

APVD Y. PETRONIN 23JUN2004

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

SEALED COPALUM ASSEMBLY, 1/0, ALU

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	134452	

CUSTOMER DRAWING	SCALE 2:1	SHEET 2 OF 2	REV N
------------------	-----------	--------------	-------

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm[Inches]	
	0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±5
MATERIAL TABLE	FINISH TABLE
-	-