

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL RELEASE	26JAN2021	SC	-
	C	REVISED PER ECR-22-156292	23JUN2021	MM	-


- 1

Mit Schraubensicherung
Loctite 243 gesichert
Locked with threadlocker
Loctite 243
- 2

Bei Erstmontage
vollstaendig einschrauben
Insert complete for
initial assembly
- 3

Oeffnungsspiel Klemmhebel
zu eingelegtem Kontakt =0.1mm
Opening clearance clamping lever
to loaded contact =0.1mm
- 4

!!! Achtung:
Vor Einsatz im Umbausatz
Maße kontrollieren und ggf.
einstellen
!!! Attention:
Check measurement before
using on conversion kit.
Too long adjusted fingers
may damage the finger
and conversion kit



POS	QTY	TE/PN	PART REV	DESCRIPTION	WEAR	SPARE
1	1	1372737-2	C	SETZFINGER INSERTION FINGER	YES	YES
2	1	1372735-5	B	KLEMMHEBEL clamping lever	YES	YES
3	1	8-547505-4	A1	Druckfeder -	-	YES
4	1	2-519011-0	B	SCREW M3x5 DIN 913 -	-	YES
5	1	3-519011-7	B	SCREW M5x8 DIN 913 -	-	YES
6	1	519051-7	A	Zyl.-Stift 2m6x8 DIN 6325 -	-	YES

XXXX marked by drawing
number, revision &
supplier symbol

XXXX Mit Zeichnungsnummer,
Revision & Herstellerkürzel
gekennzeichnet

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH -

-

DWN
M.Meyer
CHK
K. Lienert
APVD
-
PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

27JUL2017
08DEZ2020
-

CUSTOMER DRAWING

TE Connectivity

NAME
SETZFINGER KOMPLETT
INSERTION FINGER COMPLETE
-

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1372736-2

RESTRICTED TO

SCALE
2:1

SHEET
1 OF 1

REV
C

1470-19 (3/13)