




OBSOLETE	9.0	3.13	NO FLAT	1410963-9
	9.0	3.13	315°	1410963-8
	9.0	3.13	270°	1410963-7
	9.0	3.13	225°	1410963-6
	9.0	3.13	180°	1410963-5
	9.0	3.13	135°	1410963-4
	9.0	3.13	90°	1410963-3
	9.0	3.13	45°	1410963-2
OBSOLETE	9.0	3.13	0°	1410963-1
	DIM "C"	DIM "B"	DIM "A"	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.TREA 28APR2009		CHW G.GRIFFITH 28APR2009		 TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		HOUSING, KEY/ALIGNMENT PIN, VITA 41	
mm		0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ±0.013 4 PLC ± ANGLES ± FINISH		APVD G.GRIFFITH 28APR2009		-	
		1 PLC ± 2 PLC ±0.13 3 PLC ±0.013 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC		-	
MATERIAL		1 2		APPLICATION SPEC		-	
-		-		WEIGHT		-	
-		-		SIZE		A	
-		-		CODE		00779	
-		-		DRAWING NO		C-1410963	
-		-		RESTRICTED TO		-	
CUSTOMER DRAWING				SCALE		6:1	
				SHEET		1 OF 1	
				REV		A	



Technical drawing of a coin cell battery with the following dimensions and labels:

- Top Edge:**
 - Radius: $R1.0$
 - Material/Plating: 4 PLC
- Top Circular Feature:**
 - Diameter: $\varnothing 5.00 \pm 0.05$
 - Angle: A° (MEASURED CLOCKWISE)
 - Dimension: 1.60 ± 0.10
- Central Area:**
 - Text: Taiwan
 - Symbol: $\approx$
 - Dimension: 6.50
- Bottom Area:**
 - Dimension: 8.00
 - Label: -C-
- Overall Dimensions:**
 - Top Section Height: 5.25 REF
 - Bottom Section Height: 13.45
- Other Labels:** C, D



PCB LAYOUT
CONNECTOR SIDE
ALL HOLES AND FEATURES
(ARE NON PLATED THROUGH HOLES)

SHOWING 1410963-2