




LOC		DIST		REVISIONS			
REV	DATE	BY	APPV	DESCRIPTION	DATE	OWN	APPV
F				REV PER ECO 14-016435	10-30-14	CT	DH

COLUMN 1 THRU 8  
CONTACTS NOT LOADED  
EXCEPT i1, i2, i3, i4, i5, i6, i7, i8




18.6  
⊕ 0.2 ⊖ X | ⊖ S | ⊖ Z

- 1 HOUSING: LCP, UL94V0, COLOR: BLACK. CONTACT: PHOSPHOR BRONZE.
- 2 FINISH: 1.27μm GOLD IN CONTACT AREA 1.27μm MIN. TIN-LEAD ON PCB TAIL OVER 3.81μm MIN. NICKEL OVER ALL.
- 3 PLATE THROUGH HOLE PER TE PEC. 114-13056 FIGURE 4.
- 4 ADDITIONAL CONNECTOR-SIDE KEEP-OUT AREA REQUIRED IF CONNECTOR-SIDE EXTRACTION TOOL IS TO BE USED.
- 5 FINISH: 1.27μm GOLD IN CONTACT AREA 1.27μm MIN. TIN ON PCB TAIL OVER 3.81



PC BOARD LAYOUT  
(CONNECTOR SIDE)  
SCALE 5:1



5	1410966-2
2	1410966-1
PLATING	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: R. TREA 27FEB2006	TE Connectivity
DIMENSIONS: mm		CHK: G. GRIFFITH 27FEB2006	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPV: G. GRIFFITH 27FEB2006	NAME: CONNECTOR ASSEMBLY, BACKPLANE VERTICAL RECEPTACLE, CENTER, 20.3mm, MULTIGIG RT 2
0 PLC ±0.5		PRODUCT SPEC: 108-2072	
1 PLC ±0.13		APPLICATION SPEC: 114-13056	SIZE: CAGE CODE DRAWING NO: A100779C=1410966
2 PLC ±0.13		WEIGHT: -	
3 PLC ±0.13		RESTRICTED TO: -	SCALE: 8:1 SHEET 1 OF 1 REV F
4 PLC ±0.13		CUSTOMER DRAWING	
ANGLES ±1°			
FINISH: 2			