



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2000
 © COPYRIGHT 2000 BY - ALL RIGHTS RESERVED.




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	SR20-0022-01	26NOV2001	BD	JVC



NOTES


- 1) press fit area surface finish :
(B) 0.4 ... 1.5 µm Sn100 over 0.8 ... 1.3 µm Ni
- 2) contact area surface finish :
(B) 3 ± 1 µm Sn100 over 2 ± 1 µm Ni
- 3) transition area surface finish :
(B) >0.4 µm Sn100 over >0.8 µm Ni
- 4) position for the PCB after press fit process :
see Product Specification 108-90800

Contacts on strip (only for your information)



MATERIAL :
 Strip 0.64±0.01 DIN1791 CuSn6
 Tensile Strength
 Rm>560N/mm²
 R0.2>510N/mm²
 Hardness HV 180 ... 210

All dimensions are valid for the part without surface finish.
 Distances, angles, shape and position : ISO 2768-mK



1417081-1
 Part No.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 06/04/2001 B. Depoortere	TE Connectivity		
DIMENSIONS: mm		CHK -			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. Frys	PRODUCT SPEC -		
0 PLC ±		PRODUCT SPEC -	APPLICATION SPEC -		
1 PLC ±0.5		APVD -	WEIGHT 0.096 g		
2 PLC ±0.13		PRODUCT SPEC -	SIZE A3	CAGE CODE 00779	DRAWING NO C=1417081
3 PLC ±0.013		APPLICATION SPEC -	RESTRICTED TO -		
4 PLC ±0.0001		WEIGHT 0.096 g	SCALE 5:1		
ANGLES ±		CUSTOMER DRAWING	SHEET 1 OF 1		
FINISH see NOTES finish_spec_2		REV B			