





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A7		REVISED PER ECN-23-225679	08AUG2023	WLS	VS
A8		REVISED PER ECN-23-240910	24NOV2023	WLS	VS



CIRCUIT NUMBER 1



- 1 MATERIAL: HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
CONTACTS - BRASS
HOLDDOWNS - PHOSPHOR BRONZE.
- 2 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 3 PLATING: CONTACTS - 2.54µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL.
HOLDDOWNS - 2.54µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL.
- 4 COUNTERPART RECOMMENDED IS PN 1445022 OR 2008571 (DASH ACCORDING TO NUMBER OF POSITION).
- 5 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.
- 6 CUTTING EDGE, NO PLATING PRESENT IN THE REGION SHOWN.

OBSOLETE	-33.00	37.43	33.00	40.14	12	3-1445051-2
OBSOLETE	-30.00	34.43	30.00	37.14	11	3-1445051-1
OBSOLETE	-27.00	31.43	27.00	34.14	10	3-1445051-0
	24.00	28.43	24.00	31.14	9	2-1445051-9
OBSOLETE	-21.00	25.43	21.00	28.14	8	2-1445051-8
OBSOLETE	-18.00	22.43	18.00	25.14	7	2-1445051-7
OBSOLETE	-15.00	19.43	15.00	22.14	6	2-1445051-6
	12.00	16.43	12.00	19.14	5	2-1445051-5
OBSOLETE	-9.00	13.43	9.00	16.14	4	2-1445051-4
	6.00	10.43	6.00	13.14	3	2-1445051-3
	3.00	7.43	3.00	10.14	2	2-1445051-2
	DIM Z	DIM V	DIM T	DIM W	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DWN J.ROOT 08OCT2000

CHK K.WHITAKER 12-MAR-2001

APVD K.WHITAKER 12-MAR-2001

PRODUCT SPEC 108-1836

APPLICATION SPEC 114-13000

WEIGHT -

CUSTOMER DRAWING

SCALE 4:1 SHEET 1 OF 2 REV A8













STE TE Connectivity

NAME VERTICAL THRU HOLE HEADER ASSY, TIN CONTACTS, WITH THRU HOLE HOLDDOWNS, SINGLE ROW, MICRO MATE-N-LOK™

SIZE A2 CAGE CODE 00779 DRAWING NO G-1445051 RESTRICTED TO -

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-



PCB LAYOUT COMPONENT SIDE \triangle

KEYING BY POSITION SIZE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ROOT 08OCT2000	TE Connectivity			
DIMENSIONS: mm		CHK K. WHITAKER 12-MAR-2001				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K. WHITAKER 12-MAR-2001	NAME VERTICAL THRU HOLE HEADER ASSY, TIN CONTACTS, WITH THRU HOLE HOLDDOWNS, SINGLE ROW, MICRO MATE-N-LOK			
		PRODUCT SPEC 108-1836	SIZE A2	CAGE CODE 00779	DRAWING NO C-1445051	RESTRICTED TO -
MATERIAL		APPLICATION SPEC 114-13000	SCALE 4:1		SHEET 2 OF 2	REV A8
-		WEIGHT -	CUSTOMER DRAWING			