


DRAWING MADE IN AMERICAN PROJECTION

© 1971 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND OR PATENTS PENDING.

PART NO.	POS.	A	B	C	D	E
117709-1	42	4.100	.687	1.005	1.165	.527
-2	51	5.000	.687	1.005	1.165	.527

REVISIONS					DATE	APPROVED
ZONE	LTR	DESCRIPTION				
0		RELEASED PER ECN PP-0124			11-24-75	JWC



NOTES

- 1 SOLDER PLATE PER QQ-S-571
- 2 GOLD PLATE PER MIL G 45204B .000005 MIN THK OVER NICKEL PLATE PER QQ-N-290 .000100 MIN THK.
- 3 GOLD PLATE PER MIL G 45204B .000030 MIN THK.
- 4 RECOMMENDED HOLE SIZE IS "E" TYPE HOLE REFERENCE AMP SPECS 106-14018 OR 106-14019 AS APPLICABLE.
- 5 PLATING IS NOT REQUIRED ON CARRIER STRIP
- 6 ALL DIMENSIONS ARE REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES
TOLERANCES ON:
DECIMALS ± ANGLES ±


MATERIAL
BRASS
MIL-C-50

CONTRACT NO.

DP Joe DeLuca 11-24-75
CHKAPPD JWC 11/24/75
REL

DSGN APPD

OTHER APPD

AMP INCORPORATED
HARRISBURG, PENNSYLVANIA

NAME
COMB FEED THRU POST
TERMI POINT (.100)
BOARD THICKNESS .062

SIZE CODE IDENT NO. NUMBER
C 00779 117709

SCALE

SHEET

CUSTOMER DRAWING¹