


© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
✓	✓		0	DRAWN	5-7-81

**NOTES:**


- 1 COMPLIANT SECTION SEE DETAIL
2 SOLDER PLATE .000030 MIN THICK

- 4 NICKEL PLATE .000050 MIN THICK

5 POST DIAGONAL .0315/.0345

6 FOR APPLICATION IN .093/.125 THK
PC. BOARD

DIMENSION IN [] ARE METRIC



REEL NO 119518-2	13.00 [33.02]	.750 [19.05]	2.375 [60.235]	20	119513-1
	C	B	A	POS'N	PART NO
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS $\pm .005$ ANGLES $\pm 2^\circ$	CONTRACT NO DR BILLMAN 10-19-81 CHK	AMP INCORPORATED Harrisburg, Pa.			
MATERIAL COPPER ALLOY 725	APPD Andrews 5-7-81 APPD	NAME DOUBLE DENSITY (OUTTER CONTACT) COMB			
FINISH NOTES 2,3,4 AL PL PER MIL-G-45204 NI PL PER QQ-N-290	DSGN APPD OTHER APPD	SIZE C	CODE IDENT NO 00779	DRAWING NO 119513	
		SCALE		SHEET 1-1	

DEVELOPMENT ENGINEERING CONTROLLED

THIS PART IS FOR LIMITED PRODUCTION ONLY.
ABILITY TO PRODUCE IN CONTINUOUS PRODUCTION QUANTITIES FOR VARIOUS
CUSTOMERS APPLICATIONS IS NOT IMPLIED BY THIS LIMITED RELEASE.