



| LOC | DIST | REVISIONS |     |             |      |      |
|-----|------|-----------|-----|-------------|------|------|
| HB  | —    | P         | LTR | DESCRIPTION | DATE | APVD |
|     |      |           | —   | SEE SHEET 1 | —    | —    |


Ⓑ2

|            |             |                 |        |             |      |
|------------|-------------|-----------------|--------|-------------|------|
| ACTIVE     | 3-1419153-5 | PCFN-112D2M,000 | 12V    | PCFN-112D2M | k    |
| OBSOLETE   | 1-1440008-8 | PCFN-105D2M,000 | 5V     | PCFN-105D2M | j    |
| ACTIVE     | 1461193-9   | PCFN-124D2M,000 | 24V    | PCFN-124D2M | i    |
| ACTIVE     | 1461193-8   | PCFN-118D2M,000 | 18V    | PCFN-118D2M | h    |
| ACTIVE     | 1461193-7   | PCFN-109D2M,000 | 9V     | PCFN-109D2M | g    |
| ACTIVE     | 1461193-6   | PCFN-106D2M,000 | 6V     | PCFN-106D2M | f    |
| ACTIVE     | 1461193-5   | PCFN-148D2M,000 | 48V    | PCFN-148D2M | e    |
| ⓪1OBSOLETE | 1461193-4   | PCFN-124D2M,000 | 24V    | PCFN-124D2M | d    |
| ⓪1OBSOLETE | 1461193-3   | PCFN-118D2M,000 | 18V    | PCFN-118D2M | c    |
| ⓪1OBSOLETE | 1461193-2   | PCFN-109D2M,000 | 9V     | PCFN-109D2M | b    |
| ⓪1OBSOLETE | 1461193-1   | PCFN-106D2M,000 | 6V     | PCFN-106D2M | a    |
| PN STATUS  | PART NO     | DESCRIPTION     | PART B | PART A      | ITEM |

RELAY TYPE

NOTE:

Ⓑ 1.LOT NO SYSTEM AS FOLLOWING:



Ⓑ2 2.ONE CHARACTER DISTINGUISH THE LINE IDENTITY, SUCH AS: A, B...

Ⓑ2 3.TERMINAL DIMENSION IS BEFORE SOLDER DIP.

Ⓑ2 4.FOR THE TIN-PLATING OF THE PINS:  
+0.1mm FOR WIDTH,THICKNESS AND DIAMETER.  
+0.5mm FOR LENGTH.

|                  |            |                      |                     |      |
|------------------|------------|----------------------|---------------------|------|
|                  |            | EPOXY RESIN          | SEAL                | 17   |
|                  |            | POLYURETHANE Cu WIRE | MAGNETIC WIRE       | 16   |
| UL 94V-0         |            | PPS                  | CARD                | 15   |
| UL 94V-0         |            | PBT                  | CASE                | 14   |
| UL 94V-0         |            | PBT                  | BASE                | 13   |
| UL 94V-0         |            | PBT                  | BOBBIN              | 12   |
|                  | SOLDER DIP | Cu ALLOY             | COIL TERMINAL R     | 11   |
|                  | SOLDER DIP | Cu ALLOY             | COIL TERMINAL L     | 10   |
|                  |            | STAINLESS            | HINGE SPRING        | 9    |
|                  |            | Ag ALLOY             | STATIONARY CONTACT  | 8    |
|                  |            | Ag ALLOY             | MOVABLE CONTACT     | 7    |
|                  | SOLDER DIP | Cu ALLOY             | MOVABLE SPRING      | 6    |
|                  | SOLDER DIP | Cu ALLOY             | STATIONARY TERMINAL | 5    |
|                  | SOLDER DIP | Cu ALLOY             | MOVABLE TERMINAL    | 4    |
|                  | Ni PLATED  | STEEL                | CORE                | 3    |
|                  | Ni PLATED  | STEEL                | ARMATURE            | 2    |
|                  | Ni PLATED  | STEEL                | YOKE                | 1    |
| INCOMBUSTIBILITY | TREATMENT  | MATERIAL             | DESCRIPTION         | ITEM |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

MATERIAL

FINISH

DWN  
H.SASAKI

CHK  
Y.OIKAWA

APVD  
A.NAGAI

PRODUCT SPEC  
—

APPLICATION SPEC  
—

WEIGHT  
—

TE Connectivity

NAME  
  
PCFN-D2M SPEC,000

SIZE  
A3

CAGE CODE  
00779

DRAWING NO  
C-1461193

RESTRICTED TO  
—

CUSTOMER DRAWING

SCALE  
3:1

SHEET  
2 OF 2

REV  
D