


WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ("EAR") PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 4801, ET SEQ.).

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER ECN-24-286943	01OCT2024	LP	JS



NOTE:
1 USE THE LARGE OPENING IN THE LOCATOR WHEN CRIMPING THE CENTER CONTACT.

SHELLS	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
MALE CONTACT	BRASS PER ASTM B16	GOLD PLATE PER MIL-G-45204
OUTER CONTACT	PHOSPHOR BRONZE ALLOY ASTM B139	SILVER PLATE PER ASTM B700
CRIMP FERRULE	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A
SPRING WASHER	PHOSPHOR BRONZE ALLOY ASTM B139	SILVER PLATE PER ASTM B700
O-RING AND GASKETS	SILICONE RUBBER PER A-A-59588	N/A
COMPONENT	MATERIAL	FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	-

DWN
P.ESWARAMOORTHY
26SEP2024

CHK
J.A.BAKER
26SEP2024

APVD
J.SLUSSE
26SEP2024

PRODUCT SPEC
-

APPLICATION SPEC
408-2336

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
PANEL JACK BNC ASSEMBLY
TYPE E

SIZE A2	CAGE CODE 00779	DRAWING NO C-132547	RESTRICTED TO -
------------	--------------------	------------------------	--------------------

SCALE 5:1	SHEET 1 OF 1	REV D
--------------	-----------------	----------

KX23 & RG400U	220045-2	132547-1
CABLE	CRIMP TOOL	PART NUMBER

1471-9 (3/13)