







- 1 FINISH OVER INDICATED AREA: 0.000762 [.000030] MIN GOLD OVER 0.00127[.000050] NICKEL. MEETS EIA-364-53 POROSITY, MEAS. AREA .130 FROM TIP.
- 2 FINISH OVER INDICATED AREA: 0.00254[.000100]-0.00635[.000250] BRIGHT TIN-LEAD OVER 0.00127[.000050] NICKEL.
- 3 DATE CODE EITHER SIDE, WITH COUNTRY OF ORIGIN IF APPLICABLE.
- 4 "VRM Header" MOLDED INTO BOTH SIDES OF HOUSING. WITH MATTE BACKGROUND.
- 5 MATERIAL: GLASS FILLED VO THERMOPLASTIC COLOR BLACK+ CONTACT: COPPER ALLOY
- 6 RESTRICTED TO INTEL VRM PROGRAM
- 7 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- 8 FINISH OVER INDICATED AREA: 0.00254-0.00635 [.000100-.000250] MATTE TIN OVER 0.00127 [.000050] NICKEL
- 9 ROHS 2002/95/EC COMPLIANT



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. J. KNAUB 11-23-94 CHG. H. PALEY 11-23-94		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TO FRANCES: UNLESS OTHERWISE SPECIFIED: 0 PLG ± 1 PLG ± 2 PLG ± 0.13[.005] 3 PLG ± 4 PLG ± ANGLES ± FINISH		NAME ASSEMBLY, VRM 7 HEADER, MOD II, DOUBLE ROW, 2 PIECE, .100 X .100 CL, .025 SQ. POST, WITH BOARDLATCH	
		APD: H. PALEY 11-23-94 PRODUCT SPEC APPLICATION SPEC		SIZE CAGE CODE DRAWING NO. A1 00779  146205	
MATERIAL 		WEIGHT —		RESTRICTED TO —	
		  		SCALE 4:1 SHEET 1 OF 2 REV J	
CUSTOMER DRAWING					



BOARD LAYOUT FOR LATCHING AMP 2PC. RECEPTACLE