



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REV PER ECN-23-245831	03JAN2024	LP	PD

1. CONNECTOR ALLOWS FOR .060 MINIMUM AXIAL FLOAT
2. PARTS TO BE UNASSEMBLED FOR ASSEMBLY PURPOSES.



WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS
RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS
(“EAR”) PURSUANT TO 15 C.F.R. PARTS 730-774.
VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL
PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED
(TITLE 50, U.S.C., SEC. 4801, ET SEQ.).



HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	GOLD PLATE PER MIL-G-45204
BUSHING WASHER	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER SAE AMS 27000
DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT CONTACT SLEEVE	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
RETAINING RING	STAINLESS STEEL	PASSIVATED
RETAINING CLIP	BERYLLIUM COPPER PER ASTM-B-196, ALLOY C17300, CONDITION H	CADMIUM PLATE PER QQ-P-416
CONTACT RING	BERYLLIUM COPPER PER ASTM-B-194, ALLOY C17200, CONDITION H	GOLD PLATE PER MIL-G-45204
SPRING	STAINLESS STEEL	PASSIVATED PER SAE AMS 27000
COMPONENT	MATERIAL	FINISH

										1363290-2									
										PART NUMBER									
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN RUDY 2/27/98 CHK J. HAVENER 13AUG03 APVD J. HAVENER 13AUG03		 TE Connectivity													
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME		OSSP FLOATING PANEL FEEDTHRU REAR MOUNT CABLE JACK - DIRECT SOLDER ATTACHMENT (4710-5008-00)													
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005/(0.13) 4 PLC ± - ANGLES ± 1°		PRODUCT SPEC															
		APPLICATION SPEC		SIZE								CAGE CODE		DRAWING NO		RESTRICTED TO			
MATERIAL		FINISH		WEIGHT		A2		00779		C=1363290		—							
SEE TABLE		SEE TABLE		CUSTOMER DRAWING				SCALE		4:1		SHEET		1 of 1		REV		F	

1363290

E

A