



16 PRELIMINARY - NOT FOR PRODUCTION.





BASIC DIMENSIONS FOR
ODD NUMBER OF SPACES
(SEE TABLE)



DETAIL S














RECOMMENDED BOARD LAYOUT




SECTION A-A



DETAIL W
SCALE 10:1

	56mm	26.67	21	31.24	44	 8-147377-0
	44mm	13.97	11	18.54	24	 7-147377-9
	88mm	62.23	49	66.80	100	7-147377-8
	88mm	49.53	39	54.10	80	 7-147377-7
	72mm	36.83	29	41.40	60	 7-147377-6
	56mm	30.48	24	35.05	50	 7-147377-5
	56mm	24.13	19	28.70	40	 7-147377-4
	56mm	17.78	14	22.35	30	 7-147377-3
	44mm	11.43	9	16.00	20	 7-147377-2
	32mm	5.08	4	-	10	7-147377-1
	56mm	26.67	21	31.24	44	6-147377-0
	44mm	13.97	11	18.54	24	5-147377-9
	88mm	62.23	49	66.80	100	5-147377-8
	88mm	49.53	39	54.10	80	5-147377-7
	72mm	36.83	29	41.40	60	5-147377-6
	56mm	30.48	24	35.05	50	5-147377-5
	56mm	24.13	19	28.70	40	5-147377-4
	56mm	17.78	14	22.35	30	5-147377-3
	44mm	11.43	9	16.00	20	5-147377-2
	32mm	5.08	4	-	10	5-147377-1
	56mm	26.67	21	31.24	44	 3-147377-0
	44mm	13.97	11	18.54	24	 2-147377-9
	88mm	62.23	49	66.80	100	 2-147377-8
	88mm	49.53	39	54.10	80	 2-147377-7
	72mm	36.83	29	41.40	60	2-147377-6
	56mm	30.48	24	35.05	50	 2-147377-5
	56mm	24.13	19	28.70	40	 2-147377-4
	56mm	17.78	14	22.35	30	 2-147377-3
	44mm	11.43	9	16.00	20	2-147377-2
	32mm	5.08	4	-	10	 2-147377-1
	56mm	26.67	21	31.24	44	1-147377-0
	44mm	13.97	11	18.54	24	147377-9
	88mm	62.23	49	66.80	100	147377-8
	88mm	49.53	39	54.10	80	147377-7
	72mm	36.83	29	41.40	60	147377-6
	56mm	30.48	24	35.05	50	147377-5
	56mm	24.13	19	28.70	40	147377-4
	56mm	17.78	14	22.35	30	147377-3
	44mm	11.43	9	16.00	20	147377-2
	32mm	5.08	4	-	10	147377-1
FINISH	TAPE WIDTH	DIM_C	B SPACES	E	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAVI S 17MAY2017 CHK JOLSON 17MAY2017 APPV JOLSON 17MAY2017		 TE Connectivity	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±: 1 PLC ±0.3 2 PLC ±0.13 3 PLC ±: 4 PLC ±: ANGLES ±°		NAME HEADER ASSEMBLY, VERTICAL, SHROUDED, DUAL ROW W/SIDE AND END LATCHES W/O HOLD DOWNS	
MATERIAL 		FINISH SEE NOTES		SIZE A1	
		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C=147377	
				SCALE 5:1	
				SHEET 1 OF 1	
				REV H2	