





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	0	RELEASED FJ00-2107-99	3/8'00	M.H	S.M
	A	REVISED FJD0-0039-03	2JUN'03	T.S	S.M
	B	REVISED ECR ECR-19-011957	29JUL'19	A.W	R.B
	C	REVISED ECR ECR-19-016939	30OCTL'19	A.W	R.B
	D	REVISED PER ECR-25-250800	03JAN2025	F.Z	R.B



RECOMEND PC BOARD HOLE (NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS;1.6±0.1



- NOTES
- 1 MATERIAL;HOUSING:GLASS FIELD THERMO PLASTIC,POLYESTER. COLOR:BLACK CONTACT:PHOS.BRO SYSTEM RETENTION LEG : BRASS
 - 2 PRODUCT SPEC;108-5349
 - 3 QUALIFICATION TEST REPORT;501-5013
 - 4 FINISH(CONTACT AREA);0.38µm PdNi & Au PLATING OVER NICKEL
 - 5 FINISH(CONTACT AREA);0.76µm PdNi & Au PLATING OVER NICKEL
 - 6 FINISH(CONTACT); 2µMIN. TIN PLT. OVER NICKEL
 - 7 FINISH(RETENTION LEG AND CONTACT TAIL);TIN PLT. OVER NICKEL.

6	1376133-5
4	1376133-2
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.HIGO 3MAR'00	TE Connectivity		
		CHK S.MANABE 3MAR'00			
		APVD S.MANABE 3MAR'00	NAME DYNAMIC(D-3500) 4 POS. HDR. ASSY		
DIMENSIONS: mm		PRODUCT SPEC SEE 6	SIZE A3		
		APPLICATION SPEC —			
MATERIAL SEE 1		WEIGHT 4.156g	CAGE CODE 00779	DRAWING NO C-1376133	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 OF 1	REV D