





LOC		DIST		REVISIONS			
				DESCRIPTION	DATE	DWN	APVD
		F		REV PER ECO 14-003443	3-21-14	CT	DH



- △ HOUSING: LCP, UL94V0, COLOR: BLACK. CONTACT: PHOSPHOR BRONZE.
- △ FINISH: 1.27µm GOLD IN CONTACT AREA 1.27µm MIN. TIN-LEAD ON PCB TAIL OVER 3.81µm MIN. NICKEL OVER ALL.
- △ FINISH: 1.27µm GOLD IN CONTACT AREA 1.27µm MIN. TIN ON PCB TAIL OVER 3.81µm MIN. NICKEL OVER ALL.
- △ PLATE THROUGH HOLE PER TE SPEC. 114-13056 FIGURE 4.
- △ ADDITIONAL CONNECTOR-SIDE KEEP-OUT AREA REQUIRED IF CONNECTOR-SIDE EXTRACTION TOOL IS TO BE USED.



PC BOARD LAYOUT (CONNECTOR SIDE)
(SEE SHEET 2 FOR RTM)
SCALE 5:1

△ 3	1410140-2
△ 2	1410140-1
PLATING	PART NO





THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN: R. TREA 08NOV2002	CHK: J. CONSOLI 18NOV2002	APVD: J. CONSOLI 18NOV2002
mm	0 PLC ±0.5 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.13 4 PLC ±0.13	PRODUCT SPEC: 108-2072	APPLICATION SPEC: 114-13056	SIZE: A1
MATERIAL:	FINISH: #1*	WEIGHT:	CAGE CODE: 1410140	RESTRICTED TO: F
CUSTOMER DRAWING		SCALE: 2:1	SHEET: 1 OF 2	REV: F

STE TE Connectivity
CONNECTOR ASSEMBLY, BACKPLANE VERTICAL RECEPTACLE, CENTER, 20.3mm, MultiGig RT 2

LOC	DIST	REV	DATE	BY	APPV
GP	00				
REVISIONS			DESCRIPTION	DATE	BY
			SEE SHEET 1		

REAR TRANSITION MODULE APPLICATION



RTM PC BOARD LAYOUT
(CONNECTOR SIDE)
SCALE 5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN: R. TREA 08NOV2002	TE Connectivity
DIMENSIONS: mm		CHK: J. CONSOLI 18NOV2002	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: J. CONSOLI 18NOV2002	NAME: CONNECTOR ASSEMBLY, BACKPLANE VERTICAL RECEPTACLE, CENTER, 20.3mm, MultiGig RT 2
0 PLC ±0.5		PRODUCT SPEC: 108-2072	SIZE: A1
1 PLC ±0.13		APPLICATION SPEC: 114-13056	CAGE CODE: 1410140
2 PLC ±0.13		WEIGHT: -	RESTRICTED TO: -
3 PLC ±0.13		CUSTOMER DRAWING	SCALE: 2:1
4 PLC ±0.13			SHEET: 2 OF 2
ANGLES ±1°			REV: F