





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A3	ECO-19-006934	10MAY2019	AP	WS
	A4	REVISED PER ECN-22-179646	02NOV2022	WLS	VS
	A5	REVISED PER ECN-23-242776	14DEC2023	WLS	VS
	B	REVISED PER ECN-25-316179	07MAY2025	WLS	JP



- 1 MATERIAL: HOUSING - UL 94V-O RATED HIGH TEMP NYLON, COLOR BLACK.
CONTACTS - BRASS
HOLDDOWNS: - PHOSPHOR BRONZE.
- 2 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 3 PLATING: CONTACTS - 0.38 μ m MINIMUM GOLD,
OR
0.0762 μ m MINIMUM GOLD FLASH OVER 0.31 μ m MINIMUM PALLADIUM NICKEL,
ON MATING AREA PER TE CONNECTIVITY'S DISCRETION,
2.54 μ m MINIMUM MATTE TIN ON SOLDER TAILS,
ALL OVER 1.27 μ m MINIMUM NICKEL.
- HOLDDOWNS: 2.54 μ m MINIMUM MATTE TIN OVER 1.27 μ m MINIMUM NICKEL.
- 4 COUNTERPART RECOMMENDED IS PN 1445022 OR 2008571 (DASH ACC. TO NUMBER OF POSITION).
- 5 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

OBSELETE	33.00	37.43	37.00	40.14	12	3-1445088-2-
OBSELETE	30.00	34.43	34.00	37.14	11	3-1445088-1-
	27.00	31.43	31.00	34.14	10	3-1445088-0
	24.00	28.43	28.00	31.14	9	2-1445088-9
	21.00	25.43	25.00	28.14	8	2-1445088-8
OBSELETE	18.00	22.43	22.00	25.14	7	2-1445088-7-
	15.00	19.43	19.00	22.14	6	2-1445088-6
	12.00	16.43	16.00	19.14	5	2-1445088-5
	9.00	13.43	13.00	16.14	4	2-1445088-4
	6.00	10.43	10.00	13.14	3	2-1445088-3
	3.00	7.43	7.00	10.14	2	2-1445088-2
	DIM Z	DIM V	DIM Y	DIM W	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ROOT 09OCT2000 CHK K. WHITAKER 17-APR-2001 APVD C. JONES 17-APR-2001		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.20 3 PLC ±- 4 PLC ±- ANGLES ±° FINISH		NAME RT ANG THRU HOLE HEADER ASSY, 0.38Au or 0.31PdNi CNTC, THRU HOLE HOLDDOWNS, SGL ROW, MICRO MATE-N-LOK™			
		PRODUCT SPEC 108-1836 APPLICATION SPEC 114-13000		SIZE A2		CAGE CODE 00779	
MATERIAL 				DRAWING NO C=1445088		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 4:1		SHEET 1 OF 2	
						REV B	

