THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY ALL RIGHTS RESERVED.

| LOC | DIST |
|---|---|
| FT | 0 |

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|---|---|---|---|---|
| | C1 | REVISED PER ECO-11-005294 | 03MAY11 | RK | HMR |

1 MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR BLACK.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2 SUITABLE FOR 1,6-2,4mm PCB THICKNESS.

3 END-TO-END STACKABLE W/INTERLOCK, WITHOUT LOSS OF CENTERLINE SPACING.

4 WIRE SIZE RANGE: 12-30 AWG


5 RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC., FILE N° E60677.


6 IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.


7 NOT CUMULATIVE TOLERANCE.


8 WHITE INK STAMPING.

9 BUCHANAN LOGO TO APPEAR ON HOUSING, LOCATION OPTIONAL, WHERE SPACE PERMITS.







1546074-3 AS SHOWN

| DIM. A | N°POS. | PART NUMBER |
|---|---|---|
| 121.92 | 24 | 3-1546074-4 |
| 121.92 | 24 | 3-1546074-3 |
| 121.92 | 24 | 3-1546074-2 |
| 50.80 | 10 | 3-1546074-0 |
| 40.64 | 8 | 2-1546074-8 |
| 121.92 | 24 | 2-1546074-4 |
| 116.84 | 23 | 2-1546074-3 |
| 111.76 | 22 | 2-1546074-2 |
| 106.68 | 21 | 2-1546074-1 |
| 101.60 | 20 | 2-1546074-0 |
| 96.52 | 19 | 1-1546074-9 |
| 91.44 | 18 | 1-1546074-8 |
| 86.36 | 17 | 1-1546074-7 |
| 81.28 | 16 | 1-1546074-6 |
| 76.20 | 15 | 1-1546074-5 |
| 45.72 | 14 | 1-1546074-4 |
| 66.04 | 13 | 1-1546074-3 |
| 60.96 | 12 | 1-1546074-2 |
| 55.88 | 11 | 1-1546074-1 |
| 50.80 | 10 | 1-1546074-0 |
| 45.72 | 9 | 1546074-9 |
| 40.64 | 8 | 1546074-8 |
| 35.56 | 7 | 1546074-7 |
| 30.48 | 6 | 1546074-6 |
| 25.40 | 5 | 1546074-5 |
| 20.32 | 4 | 1546074-4 |
| 15.24 | 3 | 1546074-3 |
| 10.16 | 2 | 1546074-2 |

RECOMMENDED PC BOARD LAYOUT




DIMENSIONS: mm
TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.3
2 PLC ±0.25
3 PLC ±-
4 PLC ±-
ANGLES ±2
MATERIAL -
FINISH -

DWN E. ZANOLINI 5MAR2001
CHK D. BIEVENOUR 5MAR2001
APVD D. BIEVENOUR 5MAR2001
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -
CUSTOMER DRAWING

TE Connectivity

NAME TERMINAL BLOCK, PCB MOUNT ANGLED ENTRY WIRE, STACKING W/ INTERLOCK, 5.08mm, PITCH

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A3 | 00779 | C-1546074 | - |


SCALE 3:1 SHEET 1 OF 2 REV C1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY ALL RIGHTS RESERVED.


| LOC | DIST |
|---|---|
| FT | 0 |

REVISIONS


| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|---|---|---|---|---|
| | - | SEE SHEET 1 | - | - | - |





2-1546074-8 AS SHOWN





3-1546074-2 AS SHOWN




3-1546074-3 AS SHOWN




3-1546074-0 AS SHOWN




3-1546074-4 AS SHOWN

| | | | |
|---|---|---|---|
| DIMENSIONS: mm | TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- | DWN E. ZANOLIN 15MAR2001 | TE Connectivity |
| | | CHK D. BIEVENOUR 15MAR2001 | NAME TERMINAL BLOCK, PCB MOUNT ANGLED ENTRY WIRE, STACKING W/ INTERLOCK, 5.08mm, PITCH |
| | | APVD D. BIEVENOUR 15MAR2001 | |
| | | PRODUCT SPEC - | |
| | | APPLICATION SPEC - | SIZE A3 / CAGE CODE 00779 / DRAWING NO C-1546074 / RESTRICTED TO - |
| MATERIAL - | FINISH - | WEIGHT - | CUSTOMER DRAWING / SCALE 3:1 / SHEET 2 OF 2 / REV C1 |