







PROJECT NO. EGATN07138		LOC	DIST	REVISIONS					
		A1	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
				A1	SEE E-08-012925		27MAY2008	CA	VB
				A2	SEE E-08-016252		27JUN2008	CA	VB
				A3	SEE E-08-018637		24JUL2008	CA	VB
				A4	SEE E-10-019775		23SEP2010	SK	AK




- NOTES
BEMERKUNGEN
- NV NOTE NOT VALID
Bemerkung nicht verwendet
- 1 ORDER NUMBER
BESTELL-NUMMER
- 2 REVISION NUMBER
WERKZEUGÄNDERUNGS INDEX
- 3 MATERIAL MARKING
WERKSTOFFKENNZEICHNUNG
- NV GM LOGO
GM Logo
- 5 PRODUCTION DATE
PRODUKTIONS DATUM
- 6 CONTACT CAVITY NUMBER
KONTAKTKAMMERNUMMER
- 7 TE LOGO
TE Logo
- 8 PACKAGING: BULK MATERIAL IN CARDBOARD BOX
VERPACKUNG: SCHÜTTGUT IN KARTON
- 9 TOOL CAVITY MARKING
NESTMARKIERUNG

5:1

CODING A





CODING B



CODING Z

A3



A4	114-18987	SCHNITTSTELLENZEICHNUNG Interface Drawing
	929103	2 Pos. TAB 1.6x0.6 TAB-Hsg.
	1563190	2 Pos. TAB 1.6x0.6, TAB-Hsg.
TE BESTELL-NR. TE ORDER NO.		BENENNUNG DESCRIPTION
COUNTERPARTS GEGENSTECKER		

13106617	0-1241844-2	1.5	CuFe 2	PRETINNED
13106617	0-0964263-2	0.5-1.0	CuFe 2	PRETINNED
13106617	0-0964261-2	0.35-0.5	CuFe 2	PRETINNED
GM NO	STRIP ORDER NO	WIRE RANGE	MATERIAL	FINISH
		MM ²		

RECOMMENDED CONTACT SYSTEM: MICRO TIMER 2 TYPE A; UNSEALED
FOR CABLE INSULATION TYPE FLR ACC. DIN 72551 / ISO 6722 MAX. WIRE SIZE 1.5mm²
MAX. CABLE INSULATION CRIMP DIAMETER 2.9mm
FOR CABLE INSULATION TYPE TXL ACC. SAE J1128 MAX. WIRE SIZE 1.0mm² OR MAX AWG 18
THE USE OF OTHER CABLE TYPES MUST BE CHECKED IN ANY INDIVIDUAL CASE!

A4		F2-48	24414864	0-1563189-3	A	2 Pos. MT2, Rec-Hsg. CODZ	NATUR	PBT-GF20	0.9	1
		-	-	0-1563189-2	A	2 Pos. MT2, Rec-Hsg. CODB	td	PBT-GF20	0.9	1
		GF2-50	19179871	0-1563189-1	A	2 Pos. MT2, Rec-Hsg. CODA	BLACK	PBT-GF20	0.9	1
		CUSTOMER ABBR. NO	GM PART NO	PART NO	REV	DESCRIPTION	COLOR	MATERIAL	WEIGHT [g]	ITEM NO

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN		29 JUN 2007		Tyco Electronics		Tyco Electronics AMP GmbH	
mm		0.5		C44		A. Anghelescu		A. Kettler		64625 Bensheim (Germany)	
0.5		±0.5		APVD		-		NAME		2 Pos. MT2, Rec. Hsg.	
1		±0.5		PRODUCT SPEC		108-94118		SIZE		CAGE CODE	
2		±0.5		APPLICATION SPEC		114-18901		DRAWING NO		RESTRICTED TO	
3		±		WEIGHT		-		A1		00779	
4		±		CUSTOMER DRAWING		-		SCALE		5:1	
ANGLES		FINISH		SHEET		1		OF		1	
FINISH		REV		A4							