





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	L	RESIN SUPPLIER CHANGE FOR THE HOUSING	02DEC2021	SCB	KJK



SECTION X-X



6 9		OBSOLETE							
9	11		-2.54	[.100]	5.08	[.200]	2	12	8-146386-9
			99.06	[3.900]	101.60	[4.000]	40	12	8-146386-8
			96.52	[3.800]	99.06	[3.900]	39	12	8-146386-7
			93.98	[3.700]	96.52	[3.800]	38	12	8-146386-6
			91.44	[3.600]	93.98	[3.700]	37	12	8-146386-5
			86.36	[3.400]	88.90	[3.500]	35	12	8-146386-4
			83.82	[3.300]	86.36	[3.400]	34	12	8-146386-3
			78.74	[3.100]	81.28	[3.200]	32	12	8-146386-2
			71.12	[2.800]	73.66	[2.900]	29	12	8-146386-1
			68.58	[2.700]	71.12	[2.800]	28	12	8-146386-0
			66.04	[2.600]	68.58	[2.700]	27	12	7-146386-9
			60.96	[2.400]	63.50	[2.500]	25	12	7-146386-8
			58.42	[2.300]	60.96	[2.400]	24	12	7-146386-7
			55.88	[2.200]	58.42	[2.300]	23	12	7-146386-6
			50.80	[2.000]	53.34	[2.100]	21	12	7-146386-5
			45.72	[1.800]	48.26	[1.900]	19	12	7-146386-4
			43.18	[1.700]	45.72	[1.800]	18	12	7-146386-3
			40.64	[1.600]	43.18	[1.700]	17	12	7-146386-2
			38.10	[1.500]	40.64	[1.600]	16	12	7-146386-1
			35.56	[1.400]	38.10	[1.500]	15	12	7-146386-0
			7.62	[.300]	10.16	[.400]	4	12	6-146386-9
			73.66	[2.900]	76.20	[3.000]	30	12	6-146386-8
			88.90	[3.500]	91.44	[3.600]	36	12	6-146386-7
			81.28	[3.200]	83.82	[3.300]	33	12	6-146386-6
			76.20	[3.000]	78.74	[3.100]	31	12	6-146386-5
			63.50	[2.500]	66.04	[2.600]	26	12	6-146386-4
			53.34	[2.100]	55.88	[2.200]	22	12	6-146386-3
			48.26	[1.900]	50.80	[2.000]	20	12	6-146386-2
			33.02	[1.300]	35.56	[1.400]	14	12	6-146386-1
			30.48	[1.200]	33.02	[1.300]	13	12	6-146386-0
			27.94	[1.100]	30.48	[1.200]	12	12	5-146386-9
			25.40	[1.000]	27.94	[1.100]	11	12	5-146386-8
			22.86	[.900]	25.40	[1.000]	10	12	5-146386-7
			20.32	[.800]	22.86	[.900]	9	12	5-146386-6
			17.78	[.700]	20.32	[.800]	8	12	5-146386-5
			15.24	[.600]	17.78	[.700]	7	12	5-146386-4
	12.70	[.500]	15.24	[.600]	6	12	5-146386-3		
	10.16	[.400]	12.70	[.500]	5	12	5-146386-2		
9 9			5.08	[.200]	7.62	[.300]	3	12	5-146386-1
	FINISH		B		A		NO OF POSN		PART NUMBER

[illegible]

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN M.BINNER 05MNOV02 CHK J.LOJLSON 05MNOV02		 TE Connectivity			
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APPR J.LOJLSON 05MNOV02 NAME		REC.ASSY,MOD IV, SR, .100CL VRT BOARD MOUNT,CLOSED,TE SHORT PNT. OF CONTACT			
		0 P L C ± . 1 P L C ± . 2 P L C ± 0.25(.010) 3 P L C ± 0.13(.005) 4 ANGLES ± . FINISH		PRODUCT SPEC 103-25022		SIZE CAGE CODE DRAWING NO A1 00779 C 146386			
				APPLICATION SPEC 114-25018					
				WEIGHT -					
MATERIAL 		SEE TABLE		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV			