




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
J	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		D		REV PER ECO-14-017355	18NOV14	JR	TM



$\phi 1.60^{+0.1}_{-0.0}$  (PUNCHED HOLE)  
 $\phi 1.65^{+0.1}_{-0.0}$  (DRILLED HOLE)



4

2 FIG. 1

- 1 MATING CONN P/N: -1123722-
- 2 APPLICABLE P.C.B LAYOUT: SEE FIG. 1
- 3 APPLICABLE P.C.B THICKNESS: 1.60
- 4 SKETCHES SHOW NO CONTACTS MISSING.
- 5 COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF NON-METALIC MATERIAL SUPPORTING A CURRENT CARRYING CONNECTION DETAILED IN IEC 60335-1 SECTION 30 (GWT [GLOW WIRE TEST]) 750° SPEC.
- 6 PIN: MATERIAL: BRASS  
FINISH: POST TIN
- 7 HOUSING: PBT, 30% GLASS, UL94-V0
- 8 HOUSING: NYLON, 15% GLASS, UL94-V2
- 9 O : WITH PIN  
X : WITHOUT PIN

YES	8	O	O	X	O	X	O	-	-	-	-	-	19.80	21.20	23.70	NATURAL	6	7-1565606-4
NO	7	O	O	X	O	X	O	-	-	-	-	-	19.80	21.20	23.70	BLACK	6	5-1565606-4
NO	7	O	O	X	O	X	O	-	-	-	-	-	19.80	21.20	23.70	NATURAL	6	1565606-4
GWT 5	HOUSING MATERIAL	1	2	3	4	5	6	7	8	9	10	11	C	B	A	COLOR	POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± 0.5
	1 PLC ± 0.5
	2 PLC ± 0.30
	3 PLC ±
	4 PLC ±
	ANGLES ±
MATERIAL	FINISH
-	-

DWN	12JUN2014
NAGALAKSHMI K	
CHK	12JUN2014
SEILHAMER, MALACHI	
APVD	12JUN2014
SEILHAMER, MALACHI	
PRODUCT SPEC	108-5609
APPLICATION SPEC	-
WEIGHT	-



NAME				ECONOMY POWER (EP) CONN HEADER ASSY 3.96MM PITCH 6 POS SPECIAL			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
A3	MS	C-1565606	-				
CUSTOMER DRAWING			SCALE	SHEET	REV		
			-	1 OF 1	D		