



REVISIONS					
REV	DATE	BY	CHKD	APPD	DESCRIPTION
R	05AUG2016	NK	MM		REVISD PER ECO-16-006307
S	02DEC2016	RS	KM		REVISD PER ECR-16-016633



- ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
- TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
- THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING.
- HOUSING: FLAME RETARDANT THERMOPLASTIC; COLOR: BLACK.
- FINISH: 0.000381 [.000015] GOLD ON CONTACT AREA, ALL OVER 0.00127 [.000050] NICKEL ENTIRE POST.

REV	DATE	BY	CHKD	APPD	DESCRIPTION
OBSOLETE	101.19 [3.984]	99.06 [3.900]	39	40	-4-146473-0-
OBSOLETE	98.65 [3.884]	96.52 [3.800]	38	39	-3-146473-9-
OBSOLETE	96.11 [3.784]	93.98 [3.700]	37	38	-3-146473-8-
OBSOLETE	93.57 [3.684]	91.44 [3.600]	36	37	-3-146473-7-
OBSOLETE	91.03 [3.584]	88.90 [3.500]	35	36	-3-146473-6-
OBSOLETE	88.49 [3.484]	86.36 [3.400]	34	35	-3-146473-5-
OBSOLETE	85.95 [3.384]	83.82 [3.300]	33	34	-3-146473-4-
OBSOLETE	83.41 [3.284]	81.28 [3.200]	32	33	-3-146473-3-
OBSOLETE	80.87 [3.184]	78.74 [3.100]	31	32	-3-146473-2-
OBSOLETE	78.33 [3.084]	76.20 [3.000]	30	31	-3-146473-1-
OBSOLETE	75.79 [2.984]	73.66 [2.900]	29	30	-3-146473-0-
OBSOLETE	73.25 [2.884]	71.12 [2.800]	28	29	-2-146473-9-
OBSOLETE	70.71 [2.784]	68.58 [2.700]	27	28	-2-146473-8-
OBSOLETE	68.17 [2.684]	66.04 [2.600]	26	27	-2-146473-7-
OBSOLETE	65.63 [2.584]	63.50 [2.500]	25	26	-2-146473-6-
OBSOLETE	63.09 [2.484]	60.96 [2.400]	24	25	-2-146473-5-
OBSOLETE	60.55 [2.384]	58.42 [2.300]	23	24	-2-146473-4-
OBSOLETE	58.01 [2.284]	55.88 [2.200]	22	23	-2-146473-3-
OBSOLETE	55.47 [2.184]	53.34 [2.100]	21	22	-2-146473-2-
OBSOLETE	52.93 [2.084]	50.80 [2.000]	20	21	-2-146473-1-
OBSOLETE	50.39 [1.984]	48.26 [1.900]	19	20	-2-146473-0-
OBSOLETE	47.85 [1.884]	45.72 [1.800]	18	19	-1-146473-9-
OBSOLETE	45.31 [1.784]	43.18 [1.700]	17	18	-1-146473-8-
OBSOLETE	42.77 [1.684]	40.64 [1.600]	16	17	-1-146473-7-
OBSOLETE	40.23 [1.584]	38.10 [1.500]	15	16	-1-146473-6-
OBSOLETE	37.69 [1.484]	35.56 [1.400]	14	15	-1-146473-5-
OBSOLETE	35.15 [1.384]	33.02 [1.300]	13	14	-1-146473-4-
OBSOLETE	32.61 [1.284]	30.48 [1.200]	12	13	-1-146473-3-
OBSOLETE	30.07 [1.184]	27.94 [1.100]	11	12	-1-146473-2-
OBSOLETE	27.53 [1.084]	25.40 [1.000]	10	11	-1-146473-1-
OBSOLETE	24.99 [.984]	22.86 [.900]	9	10	-1-146473-0-
OBSOLETE	22.45 [.884]	20.32 [.800]	8	9	-146473-9-
OBSOLETE	19.91 [.784]	17.78 [.700]	7	8	-146473-8-
OBSOLETE	17.37 [.684]	15.24 [.600]	6	7	-146473-7-
OBSOLETE	14.83 [.584]	12.70 [.500]	5	6	-146473-6-
OBSOLETE	12.29 [.484]	10.16 [.400]	4	5	-146473-5-
	9.75 [.384]	7.62 [.300]	3	4	146473-4-
OBSOLETE	7.21 [.284]	5.08 [.200]	2	3	-146473-3-
OBSOLETE	4.67 [.184]	2.54 [.100]	1	2	-146473-2-
OBSOLETE	2.13 [.084]	-	-	1	-146473-1-

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	0.51[.02]
3 PLC	±	0.12[.005]
4 PLC	±	0.012[.0005]

ANGLES: ±

MATERIAL: 4

FINISH: 5

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIN E BRANDBERG 14MAR97

CHK G. DUBNICZKI 14MAR97

APPD G. DUBNICZKI 14MAR97

NAME: HEADER ASSEMBLY, MOD II, STACKING, SINGLE ROW, .025 SQ.POST, UNSHROUDED

PRODUCT SPEC: -

APPLICATION SPEC: -

SIZE: A1

WEIGHT: -

CUSTOMER DRAWING

SCALE: 4:1

SHEET 1 OF 1

REV S