




LOC		DIST		REVISIONS					
AD	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
		B		REVISED PER	ECO-14-000264	07JUL2014	NK	MM	

- 1 DIMENSION APPLIES OVER 99.06mm [3.900 INCHES].
- 2 HOUSING: BLACK THERMOPLASTIC, 94V-0 RATED, HIGH TEMPERATURE COMPATIBLE. POST: COPPER ALLOY.
- 3 FINISH: 0.00013[.000005] GOLD IN MATING AREA, 0.00254[.000100]–0.00508[.000200] MATTE TIN–LEAD ON SOLDER TAIL, ALL OVER 0.00127[.000050] NICKEL.
- 4 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 5 THE NOTED DIMENSION APPLIES AT INTERSECTION OF POST AND HOUSING.
- 6 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PCB.
- 7 PARTS ARE TO BE PACKAGED ON A REEL.
- 8 REELED ASSEMBLIES ARE TO BE BROKEN TO THE DESIRED POSITION SIZE AND USED AS A FUNCTIONAL SUBSTITUTE/ALTERNATIVE TO THE EXISTING AMP PART NUMBER SERIES 146090 AND 146255. THESE ASSEMBLIES ARE THE SAME IN FIT AND FUNCTION, BUT THE FORM WILL BE SLIGHTLY DIFFERENT (I.E. MOLDED HOUSING APPEARANCE AND BOW, DUE TO REELING REQUIREMENTS).
- 9 THIS PART NUMBER SPECIFIES ONE(1) LINE (i.e. PIN).
- 10 FINISH: 0.00013[.000005] GOLD IN MATING AREA, 0.00254[.000100]–0.00508[.000200] MATTE TIN ON SOLDER TAIL, ALL OVER 0.00127[.000050] NICKEL.

10	5-146855-1	9
3	146855-1	9
PLATING	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. BRANDBERG 05-SEP-97	 TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK C. SCHMID 05-SEP-97		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C. SCHMID 05-SEP-97	NAME HEADER ASSEMBLY, DOUBLE ROW, VERTICAL, REELED, CONTINUOUS —	RESTRICTED TO —
	0 PLC ± —	PRODUCT SPEC		
	1 PLC ± —	—		
	2 PLC ± 0.13 [.005]	APPLICATION SPEC		
	3 PLC ± —	—		
	4 PLC ± —	WEIGHT	SIZE	CAGE CODE
	ANGLES ± —	—	A100779	C=146855
	FINISH	—	DRAWING NO	
	SEE TABLE	CUSTOMER DRAWING	SCALE	10:1
			SHEET	1 OF 1
			REV	B