





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
G		RESIN SUPPLIER CHANGE FOR THE HOUSING	02DEC2021	SCB	KJK

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 06NOV2002	TE Connectivity Ltd.		
DIMENSIONS: mm [INCHES]		CHK J.OLSON 06NOV02			
		APVD J.OLSON 06NOV02	NAME AMPMODU, REC ASSY, MOD IV, DBL ROW, DUAL ENTRY, .100X.100CL VERTICAL MOUNT		
		PRODUCT SPEC 108-25022 APPLICATION SPEC 114-25018	SIZE A2	CAGE CODE 00779	DRAWING NO C=147099
MATERIAL 1		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 [.005] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH 2 11	WEIGHT -	RESTRICTED TO -	REV G
CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 3	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

11	99.06[3.900]	101.60[4.000]	80	12	9-147099-0
11	96.52[3.800]	99.06[3.900]	78	12	8-147099-9
11	93.98[3.700]	96.52[3.800]	76	12	8-147099-8
11	91.44[3.600]	93.98[3.700]	74	12	8-147099-7
11	88.90[3.500]	91.44[3.600]	72	12	8-147099-6
11	86.36[3.400]	88.90[3.500]	70	12	8-147099-5
11	83.82[3.300]	86.36[3.400]	68	12	8-147099-4
11	81.28[3.200]	83.82[3.300]	66	12	8-147099-3
11	78.74[3.100]	81.28[3.200]	64	12	8-147099-2
11	76.20[3.000]	78.74[3.100]	62	12	8-147099-1
11	73.66[2.900]	76.20[3.000]	60	12	8-147099-0
11	71.12[2.800]	73.66[2.900]	58	12	7-147099-9
11	68.58[2.700]	71.12[2.800]	56	12	7-147099-8
11	66.04[2.600]	68.58[2.700]	54	12	7-147099-7
11	63.50[2.500]	66.04[2.600]	52	12	7-147099-6
11	60.96[2.400]	63.50[2.500]	50	12	7-147099-5
11	58.42[2.300]	60.96[2.400]	48	12	7-147099-4
11	55.88[2.200]	58.42[2.300]	46	12	7-147099-3
11	53.34[2.100]	55.88[2.200]	44	12	7-147099-2
11	50.80[2.000]	53.34[2.100]	42	12	7-147099-1
11	48.26[1.900]	50.80[2.000]	40	12	7-147099-0
11	45.72[1.800]	48.26[1.900]	38	12	6-147099-9
11	43.18[1.700]	45.72[1.800]	36	12	6-147099-8
11	40.64[1.600]	43.18[1.700]	34	12	6-147099-7
11	38.10[1.500]	40.64[1.600]	32	12	6-147099-6
11	35.56[1.400]	38.10[1.500]	30	12	6-147099-5
11	33.02[1.300]	35.56[1.400]	28	12	6-147099-4
11	30.48[1.200]	33.02[1.300]	26	12	6-147099-3
11	27.94[1.100]	30.48[1.200]	24	12	6-147099-2
11	25.40[1.000]	27.94[1.100]	22	12	6-147099-1
11	22.86[.900]	25.40[1.000]	20	12	6-147099-0
11	20.32[.800]	22.86[.900]	18	12	5-147099-9
11	17.78[.700]	20.32[.800]	16	12	5-147099-8
11	15.24[.600]	17.78[.700]	14	12	5-147099-7
11	12.70[.500]	15.24[.600]	12	12	5-147099-6
10	11	10.16[.400]	10	12	5-147099-5
10	11	7.62[.300]	8	12	5-147099-4
10	11	5.08[.200]	6	12	5-147099-3
10	11	2.54[.100]	4	12	5-147099-2
10	11	-	2	12 6	5-147099-1
FINISH	B	A	NO OF POSN	PART NUMBER	

OBSOLETE	2	99.06[3.900]	101.60[4.000]	80	4-147099-0
	2	96.52[3.800]	99.06[3.900]	78	3-147099-9
	2	93.98[3.700]	96.52[3.800]	76	3-147099-8
	2	91.44[3.600]	93.98[3.700]	74	3-147099-7
	2	88.90[3.500]	91.44[3.600]	72	3-147099-6
	2	86.36[3.400]	88.90[3.500]	70	3-147099-5
	2	83.82[3.300]	86.36[3.400]	68	3-147099-4
	2	81.28[3.200]	83.82[3.300]	66	3-147099-3
	2	78.74[3.100]	81.28[3.200]	64	3-147099-2
	2	76.20[3.000]	78.74[3.100]	62	3-147099-1
	2	73.66[2.900]	76.20[3.000]	60	3-147099-0
	2	71.12[2.800]	73.66[2.900]	58	2-147099-9
	2	68.58[2.700]	71.12[2.800]	56	2-147099-8
	2	66.04[2.600]	68.58[2.700]	54	2-147099-7
	2	63.50[2.500]	66.04[2.600]	52	2-147099-6
	2	60.96[2.400]	63.50[2.500]	50	2-147099-5
	2	58.42[2.300]	60.96[2.400]	48	2-147099-4
	2	55.88[2.200]	58.42[2.300]	46	2-147099-3
	2	53.34[2.100]	55.88[2.200]	44	2-147099-2
	2	50.80[2.000]	53.34[2.100]	42	2-147099-1
	2	48.26[1.900]	50.80[2.000]	40	2-147099-0
	2	45.72[1.800]	48.26[1.900]	38	1-147099-9
	2	43.18[1.700]	45.72[1.800]	36	1-147099-8
	2	40.64[1.600]	43.18[1.700]	34	1-147099-7
	2	38.10[1.500]	40.64[1.600]	32	1-147099-6
	2	35.56[1.400]	38.10[1.500]	30	1-147099-5
	2	33.02[1.300]	35.56[1.400]	28	1-147099-4
	2	30.48[1.200]	33.02[1.300]	26	1-147099-3
	2	27.94[1.100]	30.48[1.200]	24	1-147099-2
	2	25.40[1.000]	27.94[1.100]	22	1-147099-1
	2	22.86[.900]	25.40[1.000]	20	1-147099-0
	2	20.32[.800]	22.86[.900]	18	147099-9
	2	17.78[.700]	20.32[.800]	16	147099-8
2	15.24[.600]	17.78[.700]	14	147099-7	
2	12.70[.500]	15.24[.600]	12	147099-6	
10	2	10.16[.400]	12.70[.500]	10	147099-5
10	2	7.62[.300]	10.16[.400]	8	147099-4
10	2	5.08[.200]	7.62[.300]	6	147099-3
10	2	2.54[.100]	5.08[.200]	4	147099-2
10	2	-	2.54[.100]	2	6 147099-1
	FINISH	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.BINNER 06NOV2002	 TE Connectivity Ltd.						
		CHK J.OLSON 06NOV02				NAME			
		APVD J.OLSON 06NOV02							
		PRODUCT SPEC							
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		108-25022		AMPMODU, REC ASSY, MOD IV DBL ROW, DUAL ENTRY, .100X.100CL, VERTICAL MOUNT			
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.13[.005] 3 PLC ± - 4 PLC ± - ANGLES ± -		APPLICATION SPEC					
				114-25018					
MATERIAL		FINISH		WEIGHT		SIZE A2	CAGE CODE 00779	DRAWING NO C=147099	RESTRICTED TO -
1		2 11		CUSTOMER DRAWING		SCALE 1:1	SHEET 2 OF 3	REV G	