



- 1 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
- 2 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADER IS HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING.
- 4 HOUSING: HIGH TEMPERATURE THERMOPLASTIC, COLOR- BLACK. CONTACT: COPPER ALLOY
- 5 FINISH: 0.000762 [.000030] GOLD ON CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN-LEAD ON SOLDER TAIL, 0.00127 [.000050] NICKEL ENTIRE POST.
- 6 FINISH: 0.000762 [.000030] GOLD ON CONTACT AREA, 0.00254-0.00508 [.000100-.000200] MATTE TIN ON SOLDER TAIL, 0.00127 [.000050] NICKEL ENTIRE POST.

RECOMMENDED PC BOARD MOUNTING DIMENSIONS FOR 1.57 [.062] THICK PC BOARD AND 0.254 [.010] STENCIL THICK.

6	24.99 [.984]	22.86 [.900]	9	20	5-1571590-1
5	24.99 [.984]	22.86 [.900]	9	20	1571590-1
FINISH	G	F	E	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIN	R BROWN	28MAY03
CHK	J GESFORD	28MAY03
APVD	J GESFORD	28MAY03
NAME	STE TE Connectivity	
PRODUCT SPEC	HEADER ASSEMBLY, MOD II, STACKING, DOUBLE ROW, .025 SQ.POST, UNSHROUDED	
APPLICATION SPEC	-	
SIZE	CAGE CODE	DRAWING NO
A1	00779	1571590
WEIGHT	-	
CUSTOMER DRAWING	SCALE	4:1
SHEET	1	OF 1
REV	C	