






LOC	DIST	REVISIONS			
		REV	DESCRIPTION	DATE	APPROVED
CM	53	1	PROPOSED	-	-

- PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.
- CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
- FLAMMABILITY V2 FOR THICKNESS 0.38mm, 1.5mm, and 3.0mm PER IEC 60695-11-10.
- GLOW-WIRE FLAMMABILITY (GWFI) 800°C FOR THICKNESS 0.38mm AND 0.75mm PER IEC 60695-2-12.
- GLOW-WIRE FLAMMABILITY (GWFI) 960°C FOR THICKNESS 1.5mm AND 3.0mm PER IEC 60695-2-12.
- GLOW-WIRE IGNITION (GWIT) 825°C FOR THICKNESS 0.38mm, 0.75mm, 1.5mm AND 3.0mm PER IEC 60695-2-13.
- PRELIMINARY - NOT FOR PRODUCTION



3-DIMENSIONAL MODEL
NTS



RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.57 [0.062] THICK P.C. BOARD

PHOSPHOR BRONZE, PRE-TIN		NYLON,UL94V-2,NATURAL		1586976-1	
PIN CONTACT MATL AND FINISH		HOUSING MATERIAL		PART NO.	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr_ruth CHK TOM MICHELUTTI APVD TOM MICHELUTTI		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0 PLC ± -		1 PLC ± -		2 PLC ± 0.13 [0.005]	
3 PLC ± -		4 PLC ± -		APPLICATION SPEC	
ANGLES		FINISH		SIZE	
SEE TABLE		SEE TABLE		A1 00779 1586976	
MATERIAL		WEIGHT		RESTRICTED TO	
SEE TABLE		—		—	
CUSTOMER DRAWING		SCALE 5:1		SHEET 1 OF 1	
				REV 1	