## SAFETY ORGANIZATIONS

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REDUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

UL RECDGNIZED: UL 1283 CSA CERTIFIED: CSA 22.2, # 0,0.4,8 VDE APPROVED: EN 133 200

#### DPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 15 AMP, 120/250 VAC,

10 AMP/40°C, 250 VAC

LINE FREQUENCY:

MAXIMUM LEAKAGE CURRENT,

EACH LINE TO GROUND:

9.6 µA **@** 120V 60Hz 16.6 µA **@** 250V 50Hz

OPERATING AMBIENT TEMP. RANGE: -10°C TO +40°C @ RATED CURRENT, Ir.

IN AN AMBIENT, To, HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT, Io, IS AS FOLLOWS:

100 - To  $I_0 = I_r -$ 60

### RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: -40°C TO +85°C HUMIDITY: 21 DAYS @ 40°C 95% RH. CURRENT OVERLOAD TEST: 6 TIMES In FOR 8 ZECONDS

#### CUSTOMER DRAWING CATALOG # 15SRB1-R ECN # JAPPRVD. DATE PJD 02MAY07

# TEST SPECIFICATIONS:

INDUCTANCE: N/A mH

CAPACITANCE: (MEASURED @ IKHz, 0.250VAC MAX., 25°C±1°C)

LINE TO GROUND: LINE TO LINE: 100pF ± 20% N/A

DISCHARGE RESISTOR: N/A L/G AND L/L I.R.

NO DISCHARGE RESISTOR:

6000M (MIN.) @ 100VDC,


20°C AND 50% RH

### RECOMMENDED RECEIVING INSPECTION HIPDT:

LINE TO GROUND: 1500 VAC FOR I MINUTE 1450 VDC FDR | MINUTE LINE TO LINE:

# FILTER APPROVAL:

THE BEST WAY TO SELECT AND BUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



<u>50∧</u> -	50a-50a(MINIMUM) INSERTION LOSS						
FREQUENCY MHz	1.0	5.0	10	50	100	300	
CDMMON	/	/	/	3	6	22	
DIFF. dB	/	/	/	/	/	/	

THIRD ANGLE PROJECTION LINLESS OTHERWISE SPECIFIED, TOLERANCE TO BE ±.025

MATERIAL & FINISH: AS SUPPLIED

This document is proprietory to CORCOM IN and is not to be reproduced nor used for nanufacturing purposes except on EDREBH'S prior written consent.

/Electronics ##COFCOM 620 S. BUTTERFIELD RO. HUNDELETH IL 60060

# POWER LINE FILTER

r	CAD FILE: G: \	CON155RB2-ROO	TYCD # 4-6609987-7	
-	SCALE: 75.	DATE: 18.JANO6	CAYALOG NO.	REV.
: 1	DRW. RY:	COLLEGIS	15SRB2-R	l n
	SO	0K16: P.ID	199KDZ-K	U
_				·