





- 1 SPECIFICATIONS:
MAGNET WIRE #18 - #34 AWG,
.006"(0.16MM)–.040"(1.02MM) DIA COPPER.
OTHER SIZES MAY BE ACCOMMODATED,
CONSULT TYCO ELECTRONICS FOR APPROVAL.
MALE BLADE .020" (0.5mm) THICK BRASS
- 2 POCKET RECOMMENDATION: #1601426
- 3 TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS
SPECIFICATION 114–13166 FIGURE 11.
- 4 PRELIMINARY – NOT FOR PRODUCTION
- 5 TWO (2) TERMINALS SHOWN FOR ILLUSTRATION PURPOSES ONLY.
- 6 PRE–PRODUCTION – FASR REQUIRED.
- 7 PRODUCT SPECIFICATION TO COMPLY WITH 108–2293



N/A	UNPLATED	4-1601196-5
N/A	UNPLATED	6-1601196-5
N/A	POST TIN OVER NICKEL	6-1601196-3
N/A	POST TIN OVER NICKEL	4-1601196-3
N/A	UNPLATED	9-1601196-1
N/A	UNPLATED	8-1601196-1
N/A	UNPLATED	6-1601196-1
CORRUGATED REEL	UNPLATED	2-1601196-1
CORRUGATED REEL	UNPLATED	1601196-4
PLASTIC REEL	POST TIN OVER NICKEL	1601196-3
CORRUGATED REEL	POST TIN OVER NICKEL	1601196-2
CORRUGATED REEL	UNPLATED	1601196-1
REEL	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MICHAEL S. FEHER 25MAY2004	TE Connectivity	
		CHK GENE JACONO 25MAY2004		
		APVD GENE JACONO 25MAY2004	NAME	
		PRODUCT SPEC 108-2085	STANDARD RANGE HIGH CARRIER WIRE TO BLADE SIAMEZE TERMINAL	
		APPLICATION SPEC 3		
MATERIAL BRASS, SPRING HARD		FINISH SEE TABLE	WEIGHT 0.10	SIZE A2
			CAGE CODE 00779	DRAWING NO C=1601196
			CUSTOMER DRAWING	RESTRICTED TO -
			SCALE 1:1	SHEET 1 OF 1
				REV B7