



P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	ECR-16-001537	12JUL2016	KG	DW
	E	ECR-17-001574	12APR2017	KG	DW

1. USE WITH FERRULE KIT P/N 1588908-2 (125um), 1588908-3 (125.5um), OR 1588908-1 (126um), ONE EACH PER CAVITY, PC-POLISH.
2. PROTECTIVE LABEL APPLIED AFTER FINAL CLEAN ROOM TEST TO PREVENT OPTICAL CAVITY CONTAMINATION. REMOVE ONLY WHEN READY TO ASSEMBLE.
3. FOR USE AT BOTH 1310 AND 1550nm WAVELENGTHS.



1516233-1 SHOWN



1516233-1 1516233-2 1516233-3 1516233-4

VIEW X - X

OBSOLETE	2 CHANNEL SM	1516233-4
	2 CHANNEL MM	1516233-3
	4 CHANNEL SM	1516233-2
	HYBRID, 2MM + 2SM CHANNELS	1516233-1
	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	-

MATERIAL

STAINLESS ALLOYS & NBR

DWN: K. GLATFELTER 01APR2009

CHK: D. WERTMAN 01APR2009

APVD: D. WERTMAN 01APR2009

PRODUCT SPEC: -

APPLICATION SPEC: -

WEIGHT: -

CUSTOMER DRAWING

TE Connectivity

NAME: INSERT ASSEMBLY, SPECIAL, IF, PRO BEAM JR.

SIZE: A200779

CAGE CODE: C-1516233

DRAWING NO: -

RESTRICTED TO: -

SCALE: 4:1

SHEET: 1 OF 1

REV: E